

Filter WDMs (660 - H Series)

CORNING

Features and Benefits

High Isolation

Low Insertion Loss

Bi-directional

Completely Passive

Epoxy-Free Optical Path

Corning offers the 660 - H Series of filter WDM products which utilize high-performance thin film interference filters to provide exceptional bandpass performance. The filter WDM is a bi-directional component optimized for a variety of applications including erbium doped fiber amplifiers. Corning's products offer minimal insertion loss and high isolation. They also offer stable and reliable performance over a broad temperature range.

Standards

RoHS	Free of hazardous substances according to RoHS2011/65/EU
Design and Test Criteria	Product is qualified to Telcordia GR-1209-CORE and GR-1221-CORE



Filter WDMs (660 - H Series)



Specifications

Parameters	
Wavelength Range	1450-1490 nm or 1535-1580 nm
Pass Channel Insertion Loss	< 0.6 dB
Reflect Channel Insertion Loss	< 0.4 dB
Pass Channel Isolation	> 30 dB
Reflect Channel Isolation	> 12 dB
Return Loss	> 45 dB
Directivity	> 50 dB
PDL	< 0.1 dB
PMD	< 0.1 ps
Maximum Optical Power	300 mW
Operating Temperature Range	-5°C to +65°C
Storage Temperature Range	-40°C to +85°C
Tensile Load (900 µm Buffered)	5N Maximum

Shipping Package		
Packaging Dimensions	Fiber Type	Pigtail Length
38 mm x 5.0 Φmm (Not including boots)	Fiber Type: Corning® SMF-28e® or compatible	1 m (Standard)

Filter WDMs (660 - H Series)

CORNING

Ordering Information

Filter WDMs (660 - H Series)

6 6 0 - 2 - 2

1 2 3 4 5

1 Select Wavelength Range
H: 1480/1550 nm

2 Select Mode
1: Short Pass/Long Reflect
2: Long Pass/Short Reflect

3 Select Pigtail Type
0: 250 μ m Tube
1: 900 μ m Tube
2: 250 μ m Box
3: 900 μ m Box

4 Select Connector*
A: None
L: LC/PC
P: FC/PC
Q: FC/APC
S: SC/PC
T: SC/APC
U: MU/PC

5 Select Customization
000: Standard or
Running number used for
special types or custom made

Note:

* Specifications do not include connector loss.

These part numbers are specific to Corning Optical Communications OEM Solutions Business Unit. Please contact OEM sales at +1-408-736-6900 or oemsales@corning.com and visit www.corning.com/opcomm/oem for sales support.



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-408-736-6900 • www.corning.com/opcomm/oem • Email: oemsales@corning.com

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2016 Corning Optical Communications. All rights reserved.

Spec Sheet CAH-128_AEN
Page 3 | Revision date 2016-11-23

CORNING