

CORNING

FROST & SULLIVAN

BEST
2018 PRACTICES
AWARD

ASIA-PACIFIC
DATA CENTER
ENABLING TECHNOLOGY LEADERSHIP AWARD

Discover why best-in-class data centers choose Corning.

Now EDGE8® Solutions Deliver Even More Value

Corning's award-winning EDGE8® solution is the industry's first modular, tip-to-tip optical cabling system to feature a Base-8 design to maximize per-rack-unit density for better network scalability and improved link performance. And now our EDGE8 solutions deliver even more value – more applications, more security, more options, more flexibility, and more ways to seamlessly migrate to 40, 100, and even 400G.



MORE APPLICATIONS



EDGE8 FX Housing



Overhead and Subfloor Distribution

MORE SECURITY



EDGE8 Secure Solutions



EDGE8 Armored Trunks


MORE OPTIONS



EDGE8 High-Fiber-Count Trunks



EDGE8 Port Replication Housing



EDGE8 Port Tap Modules and Harnesses

MORE FLEXIBILITY



EDGE8 LC Panels



Legacy EDGE™ Housing Compatibility



EDGE8 Hybrid Trunks



Mesh Module

Visit us at our booth or learn more at: corning.com/opcomm