



STAY in the
LOOP



SEE the
LIGHT
FIBER OPTIC TRAINING

SEE the LIGHT® Fiber Optic Training

As a leader in the fiber optics industry, Corning is committed to educating customers by providing quality real-world training on the latest products and applications. See the Light Fiber Optic Training has expanded to include webinars, seminars, and certified training by Corning experts.

Whether you need formal fiber training or are just looking to grow your knowledge base, See the Light Training offers something for everyone and every schedule!

Webinars

These one-hour learning experiences facilitated by Corning experts combine a mix of solutions, product discussions, and demonstrations relevant to today and tomorrow's fiber optic industry. Customer webinars are available upon request based on resource availability. Contact your local sales representative or email stlinfo@corning.com for more information.

- Webinar training on a variety of topics
- Recorded webinar topics available on-demand
- Video demonstrations by product experts
- Monthly webinars on a variety of topics
- Online meetings save time and money



Register for recorded or live webinars at www.corning.com/opcomm/webinars

Seminars



See the Light Seminars bring a variety of topics and the latest technology in the industry to a city near you. These three-to six-hour trainings, taught by Corning experts, allow students to work hands-on with equipment and materials ideal for installation, termination, troubleshooting, and system design.

- Seminars keep employees up-to-date and on the job
- Variety of fiber optic topics offered monthly
- Hands-on fiber optic product training and demonstrations
- Industry continuing education credits may apply

Certified Training

Corning has developed comprehensive, integrated training to meet the needs of designers, installers, and end users of fiber optic products. Our multiday courses have been approved by industry-recognized associations such as BICSI, ETA, and FOA and include hands-on installation and design classes for local area networks, installation, testing, and design. Continuing education credits and certifications are available. Additional fees may apply.



- Courses available: Corning Fiber Installation (CFI), Corning Fiber Design (CFD), and Corning Fiber Testing and Troubleshooting (CFTT)
- Condensed two- to three-day format for less schedule/work disruption
- Extensive hands-on system build and troubleshooting
- Industry continuing education credits may apply

Which Training is Right for You?

Customer Needs	National Webinars	Customer Webinars	Seminars	Certified Training
On-demand Training	■			
To Learn More Products and Solutions	■	■	■	■
Continuing Education Credits (CECs)			■	■
Hands-on Training			■	■
NPI Ed Credits or Other Industry Certification	■	■	■	■
On-site Training*	■	■		■
Free Training**	■	■	■	

*On-site certified training is based on availability.

**Some seminar topics may have enrollment fees.



Don't see what you are looking for?
 Contact the See the Light Fiber® Optic Training team at
stlinfo@corning.com or visit www.corning.com/opcomm/STL

CORNING

Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA
 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2014 Corning Optical Communications. All rights reserved. Published in the USA. LAN-1770-AEN / October 2014

**SEE the
 LIGHT®**
 FIBER OPTIC TRAINING