



Transforming Manufacturing Connectivity

AI, IoT, and robotics will shape tomorrow's industrial networks

Industry 4.0 needs fiber

Representing a significant leap in industrial capability, Industry 4.0 integrates advanced technologies to create highly efficient, automated systems. For manufacturers, this rapidly evolving connectivity landscape demands robust infrastructure capable of handling surging data volumes quickly and reliably. More than just connectivity, fiber optics are **the backbone of a new industrial age**.



Future-Ready: Reliable connectivity and sustainable network infrastructure support increasing reliance on digital technologies.



Resilience in Harsh Environments: Withstands the rigors of clean rooms and harsh industrial settings while ensuring the security and minimal disruptions required by facilities like semiconductor FABs or battery plants.



High Bandwidth and Low Latency: Enables rapid, seamless data transfer crucial for real-time monitoring and control at smart factories.



Sustainability and Scalability: Greater flexibility and energy efficiency than traditional copper cables allowing operations upgrades without overhauling network infrastructure.



Reduced Maintenance Cost: Longer life span and less susceptible to interference and degradation for less maintenance and lower operational costs over time.


Corning's advanced fiber optics technology is an essential driver for Industry 4.0

We offer unparalleled connectivity to support the high bandwidth and low latency demands of smart manufacturing processes, where precision and data management are critical.

Core LAN & Harsh FAN

Available, Compatible, Reliable

Local Area and Factory Area Networks
Fiber Cable, Hardware, Connectivity



Long Reach & Optical LAN

Data & Power Beyond 600 Meters


ActiFi® Hybrid Cable, Corning Intelligent Power, 10G HPoE Fiber
Media Converters & Software Defined LAN



Campus & Utility Networks

Industrial Grade, Ruggedized

OSP, LSZH™, Tray Grade, Mining & Petrochemical, and Rodent
Resistant Cables Below and Above-Grade Fiber Closures



Pre-Term & Microcables

Reduce Time, Labor, Disruption


Ruggedized, durable, IP68-rated Pushlok® and Evolv® Terminals,
MiniXtend® MicroCables



EDGE™ Data Center

Reliable, Scalable, Manageable

Plug & Play™, EDGE™, and EDGE8®, EDGE Rapid Connect



To learn more about Corning's high-performance solutions for Industry 4.0, visit www.corning.com/industrial

CORNING

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC 28216 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification.
A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners.
Corning Optical Communications is ISO 9001 certified. © 2024, 2025 Corning Optical Communications. All rights reserved. LAN-3316-AEN / May 2025