

Wall-Mountable Splice Housings (WSH)

CORNING

Features and Benefits

Front door can be used as a work surface
Convenience for splicing

Use with LANscape® Solutions WCH-12P
System compatibility

Provides midspan access capability
System access

Universal cable clamp
Cable strain-relief

Standards

RoHS

Free of hazardous substances according to RoHS 2002/95/EG


Corning wall-mountable splice housing (WSH) provides storage and protection of fiber splices in individually accessible trays. The wall-mountable housing is designed to store the optical fibers being spliced within the tray and can accommodate either 16 0.2-in (Type 2S or 2R) or 11 0.4-in (Type 4S or 4R) splice trays.

The front door of the housing is a work surface that can support the weight of a fusion splicer and features a lip around the door to help retain loose items. Multiple cable entry/exit locations are provided on the top and bottom and grommets prevent dust from entering the housing. Depending on the entry location of the cables into the housing, the strain-relief bracket can be moved to a variety of positions. The design also includes the Corning universal cable clamp and provisions for mounting an optional grounding kit.

The WSH can be used in conjunction with a wall-mountable connector housing (WCH) for termination. The cable entry/exit locations line up with cable entries on the WCH-12P.



Wall-Mountable Splice Housing



Wall-Mountable Splice Housing

CORNING

Wall-Mountable Splice Housings (WSH)



Specifications

Ordering Information | *Note: Contact Customer Care at 1-800-743-2675 for other options.*

Part Number	Product Description	Units per Delivery
WSH-11SPT-F	Wall-Mountable Splice Housings (WSH), for up to (11) 0.4-in (Category 4S, 4R or 4A) splice trays	1/1
WSH-16SPT	Wall-Mountable Splice Housings (WSH), for up to (16) 0.2-in (Type 2S, 2R or 2A) splice trays	1/1
WSB-48FI	Holds four 12-in splice organizer trays (Corning p/n: QFMQNC12Q)	1/1

Splice trays must be ordered separately

Accessories

Part Number	Product Description	Units per Delivery
GROUND-KIT-2	WSH Grounding Kit; it includes a grounding bar and hardware	1/1
BKT-ALL-R23-75	Universal Rack-Mount Bracket used for 19-in or 23-in equipment racks. Allows for rack-mounting of the wall-mountable units	1/1
HDWR-LOCK-KIT	Lock Kit for front door of housing; contains one lock with two keys	1/1



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2014 Corning Cable Systems. All rights reserved.

