

# Wall-Mountable Interconnect Centers (WIC)

CORNING

## Features and Benefits

### Patented universal cable clamp

Cable strain-relief

### Durable metal housing

Protection

### Lockable doors

System security

### Routing guides

Fiber management

## Standards

RoHS

Free of hazardous substances according to RoHS 2002/95/EG

Corning Cable Systems Wall-Mountable Interconnect Center (WIC) is an economical housing for terminating optical fiber cables. It provides protection for the connectors in the physical plant environment and is ideal for use in building entrance rooms, telecommunication rooms, or inside programmable logic controller cabinets typically found in manufacturing plants. The durable black metal housing can be mounted in stacked and/or reversed positions and there is an optional cover available for jumper protection with lockable doors. Strain-relief is accomplished with the patented universal cable clamp and routing guides are included for fiber management. The WIC-02P accepts two standard CCH connector panels and the WIC-04P accepts four panels or modules. Both housings include splicing provisions for Corning Cable Systems Type 2R or 4R Splice Trays and accept the standard CCH connector panels, CCH pigtail panels or CCH Plug & Play™ Systems connector modules.



WIC-02P and WIC-04P (WIC-04P shown with optional subscriber door)



WIC-04P (shown with pigtail splicing and optional jumper protection door)

CORNING

# Wall-Mountable Interconnect Centers (WIC)

CORNING

## Specifications

### Ordering Information | *Contact Customer Care at 1-800-743-2671 for other options.*

Part Number	Product Description	Units per Delivery
WIC-02P	Wall-Mountable Interconnect Center (WIC), holds 2 CCH connector panels	1/1
WIC-04P	Wall-Mountable Interconnect Center (WIC), holds 4 CCH connector panels	1/1

## Accessories

Part Number	Product Description	Units per Delivery
HDWR-LOCK-KIT	Lock Kit for front door of housing; contains one lock with two keys	1/1
HDWR-LOCK-KIT-2	Lock Kit, Field-Installable, includes 1 lock and key; keyed different from HDWR-LOCK-KIT	1/1
CCH-BLNK	Blank Panel, compatible with LANscape® Solutions Housings	1/1
WCH-STRNRLF-KIT	Optional External Cable Strain-Relief Kit; it utilizes Corning Cable Systems Universal Cable Clamp; includes bracket, mounting hardware, 1 strain-relief clamp and 1 multicable insert that will hold up to 5 cables less than 0.4 in diameter	1/1



Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/cablesystems](http://www.corning.com/cablesystems)

A complete listing of the trademarks of Corning Cable Systems is available at [www.corning.com/cablesystems/trademarks](http://www.corning.com/cablesystems/trademarks).

Corning Cable Systems is ISO 9001 certified. © 2013 Corning Cable Systems. All rights reserved.

CORNING