

CP-600 Station Protector Housing

CORNING

Features and Benefits

TandAction™ Hybrid Station Protector or 3-element gas tube

Advanced IDC terminations with superior surge protection protect valuable electronics

Weather-resistant housing design

Wire terminations protected for long life

Compact, low-profile housing

Allows installation and access in small spaces

Modular design

Protectors can be added in the field as needed

The CP-600 Series Station Protector Housing is designed to accommodate one to six station protectors. The compact size and aesthetic appeal of the CP-600 makes it ideal for residential installations.

This station protector housing is available with the SPD 356-XY Hybrid TandAction™ screw terminal or the USP-123 Series sealed IDC station protectors.

The housing is molded from an engineering-grade thermoplastic selected to withstand harsh outdoor environments. The housing may be installed on a wall or secured to a vertical conduit. Unauthorized access is deterred by the security screw latch. For added security, a lock may be installed on the integrated locking hasp.



CP-600 Protector Housing (open)
| Photo PIM0065



CP-600 Protector Housing (closed)
| Photo PIM0066

CORNING

CP-600 Station Protector Housing

CORNING

Specifications

	Dimensions (HxWxD)	Weight
CP-600 Series	21.6 cm x 20.3 cm x 6.4 cm (8.5 in x 8 in x 2.5 in)	0.7 kg (1.6 lb)

Shipping Information

	Quantity	Dimensions (HxWxD)	Shipping Weight
CP-600 Series	14	40.6 cm x 40.6 cm x 22.9 cm (16 in x 16 in x 9 in)	10.5 kg (23 lb)

Ordering Information

CP - 6 0 -
 1 2 3

1 Select telco security.

0 = Hex head 1 = KS screw

2 Select number of protectors.

1 = 1 protector 4 = 4 protectors
2 = 2 protectors 5 = 5 protectors
3 = 3 protectors 6 = 6 protectors

3 Select station protector option.

Code	Part Number	Description
N0	SPD 356-XV	TandAction Hybrid, 3-element, 356 studded
Z0	SPD 356-XY	TandAction Hybrid, 3-element, 356 studded
BH	SPD 356-KY-S	3-Element Gas Tube, no backup air gap, 356 sealed

Corning Cable Systems LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/cablesystems

A complete listing of the trademarks of Corning Cable Systems is available at www.corning.com/cablesystems/trademarks.

Corning Cable Systems is ISO 9001 certified. © 2013 Corning Cable Systems. All rights reserved.

CORNING