

MiniXtend® Cable, LT, A-DQ(ZN)2Y

CORNING

Corning MiniXtend products are fiber optic stranded loose tube or central tube fully dielectric outdoor cable typically used in Long-Haul, Metro- or Access Networks when limited space is available.

With the dual layer tube design and low friction PE sheath MiniXtend cables are optimized for blowing and best used in mini or micro ducts.

The buffer tubes and fiber in each tube are color-coded for quick and easy identification. MiniXtend are available with Corning Single Mode Fiber SMF 28e+® & SMF 28e® ULTRA (ITU-G 652D) or bend improved ClearCurve® fibers (ITU-G 657).

Features and Benefits

Reduced outer cable diameter

High fiber density in microduct systems

Compact and light

CapEx-optimized installations and upgrades

Optimized cable stiffness

Long installation lengths

Fully dielectric

No grounding required

Color-coded tubes and fibers

Easy identification of tubes and

SMF-28e+® according to ITU-T G.652.D

Transmission security, low attenuation and polarization mode dispersion



MiniXtend® Cable, LT, A-DQ(ZN)2Y

MiniXtend® Cable, LT, A-DQ(ZN)2Y

CORNING

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Specifications

General Specifications

Environment	Outdoor
Product Type	Dielectric
Cable Type	Stranded Loose Tube

Temperature Range

Temperature Range, Storage	-30 °C - 70 °C (-22 °F - 158 °F)
Temperature Range, Installation	-5 °C - 40 °C (23 °F - 104 °F)
Temperature Range, Operation	-30 °C - 70 °C (-22 °F - 158 °F)

Design Characteristics Cable

Fiber Count	Fibers per Tube	Number of Tube Positions	Number of Active Tubes	Buffer Tube Diameter
12 -	12	6	1 - 6	1.4 mm
96	12	8	8	1.4 mm
144	12	12	12	1.4 mm

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Crush Resistance	Max. Tensile Strength, Short-Term	Cable Weight
12	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	23 kg/km

MiniXtend® Cable, LT, A-DQ(ZN)2Y

CORNING

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Min. Bend Radius Installation	Min. Bend Radius Operation	Crush Resistance	Max. Tensile Strength, Short-Term	Cable Weight
	5.3 mm	106 mm	80 mm	1000 N/10 cm	350 N	
24	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	23 kg/km
	5.3 mm	106 mm	80 mm	1000 N/10 cm	350 N	
36	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	23 kg/km
	5.3 mm	106 mm	80 mm	1000 N/10 cm	350 N	
48	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	23 kg/km
	5.3 mm	106 mm	80 mm	1000 N/10 cm	350 N	
60	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	23 kg/km
72 -	5.3 mm	106 mm	79.5 mm	1000 N/10 cm	350 N	
	5.3 mm	106 mm	80 mm	1000 N/10 cm	350 N	
96	6.3 mm	126 mm	94.5 mm	1000 N/10 cm	1000 N	35 kg/km
144	8 mm	160 mm	120 mm	1000 N/10 cm	1000 N	55 kg/km

Transmission Performance

Single-mode

Fiber Name	Bend-Improved Single-mode (OS2)	Single-mode (OS2)
Performance Option Code	20	22
Fiber Category	OS2	OS2
Wavelengths	1310 nm / 1383 nm / 1550 nm	1310 nm / 1383 nm / 1550 nm
Fiber Code	Z	E
Maximum Attenuation	0.34 dB/km / 0.34 dB/km / 0.20 dB/km	0.36 dB/km / 0.36 dB/km / 0.22 dB/km

MiniXtend® Cable, LT, A-DQ(ZN)2Y

The Corning logo consists of the word "CORNING" in a white, serif, all-caps font, centered within a solid blue square.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2025 Corning Optical Communications. All rights reserved.