

ALTOS® Lite Loose Tube, Gel-Free, Single-Jacket, Single-Armored Cables with FastAccess® Technology

CORNING

Corning ALTOS® Lite gel-free, single-jacket, single-armored cables with FastAccess® technology are designed for direct-buried installations. The innovative FastAccess technology feature combined with the gel-free loose tube design simplifies removal of the cable jacket and accessing the buffer tubes. The gel-free design means the cables are fully waterblocked using craft-friendly water-swellable materials which makes cable access simple and require no clean up. The loose tube design uses Corning's SMF-28® Ultra fiber to provide reliable transmission parameters for a variety of voice, data, video and imaging applications. The flexible buffer tubes are easy to route in closures, and the SZ-stranded, loose tube design isolates fibers from installation and environmental rigors while allowing easy midspan access. The single-armored construction provides additional crush and rodent protection. These cables have a medium-density polyethylene jacket that is rugged, durable and easy to strip.

Features and Benefits

ALTOS® Lite FastAccess® Technology

Corning's ALTOS Lite FastAccess Technology refers to the combination of a Corning FastAccess Technology jacket with an innovative technology used to bind cable construction through the manufacturing process, eliminating the use of binder yarns and waterblocking tapes and up to a 60 percent improvement in cable access time. These technologies also reduce the overall risk of inadvertent fiber damage by reducing the need for sharp cable access tools.

Stranded optical core

Elimination of overlapping yarn binders around stranded tubes to reduce end access time

Fully waterblocked loose tube all-dielectric gel-free design

Simple access and no clean up

Single-armored construction



Provides additional crush and rodent protection

Polyethylene jacket

Rugged, durable and easy to strip (while providing superior protection against UV radiation, fungus, abrasion and other environmental factors)

Available with Corning's SMF-28® Ultra fiber

ITU-T G.652 D and ITU-T G.657 A1 compliant fiber ready for any application



ALTOS® Lite Loose Tube, Gel-Free, Single-Jacket, Single-Armored Cables with FastAccess® Technology

CORNING

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Specifications

General Specifications

Environment	Outdoor
Product Type	Armored
Cable Type	Loose Tube

Temperature Range

Temperature Range, Storage	-40 °C - 70 °C (-40 °F - 158 °F)
Temperature Range, Installation	-30 °C - 70 °C (-22 °F - 158 °F)
Temperature Range, Operation	-40 °C - 70 °C (-40 °F - 158 °F)
Notes	Corning recommends storing cable in a proper temperature environment prior to installation to allow the cable temperature to meet installation temperature range specifications for best installation results.

Design Characteristics Cable

Fiber Count	Fibers per Tube	Number of Tube Positions	Number of Active Tubes	Buffer Tube Diameter
12 - 72	12	6	1 - 6	2.5 mm

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Min. Bend Diameter Installation	Min. Bend Diameter Operation	Cable Weight
12	11.7 mm	2700 N	890 N	352 mm	234 mm	116 kg/km

ALTOS® Lite Loose Tube, Gel-Free, Single-Jacket, Single-Armored Cables with FastAccess® Technology

CORNING

Mechanical Characteristics Cable

Fiber Count	Nominal Outer Diameter	Max. Tensile Strength, Short-Term	Max. Tensile Strength, Long-Term	Min. Bend Diameter Installation	Min. Bend Diameter Operation	Cable Weight
24	11.7 mm	2700 N	890 N	352 mm	234 mm	117 kg/km
36	11.7 mm	2700 N	890 N	352 mm	234 mm	118 kg/km
48	11.7 mm	2700 N	890 N	352 mm	234 mm	119 kg/km
60	11.7 mm	2700 N	890 N	352 mm	234 mm	120 kg/km
72	11.7 mm	2700 N	890 N	352 mm	234 mm	121 kg/km

Z
U
C
-
T

F
2
2
D
2
0

1 Select fiber count.
Standard offerings: 12-72 fibers

2 Defines fiber type.
Z = Single-mode SMF-28® Ultra fiber (G.652.D/G.657.A1)

3 Defines cable type.
U = ALTOS loose tube cable with 2.5 mm buffer tubes

4 Defines outer jacket.
C = Single-jacket, single-armored

5 Defines fiber placement.
T = 12 fibers/buffer tube

6 Select length markings.
3 = Markings in meters
4 = Markings in feet

7 Defines special jacket feature.
F = FastAccess® Technology

8 Defines performance option code.
22 = Single-mode (OS2)
Max. attenuation 0.34/0.34/0.20 dB/km

9 Defines cable type.
D = Gel-free cable

10 Defines special requirements.
20 = No special requirements



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2025 Corning Optical Communications. All rights reserved.