

# CCHE Splice Module with Pigtails



CORNING

Closet Connector Housing (CCHE) pigtailed splice cassettes enable faster field splicing and easy modular management of connectorization within the housing. They are preloaded and pre-routed for quick fusion splicing of either individual or ribbon fibre pigtails, using the same space-saving platform as the standard CCHE splice cassette.

The pre-routed pigtailed cassettes reduce field labor by streamlining features and components to allow for efficiencies in the field. They are prepped with a 2 m pigtail assembly with all pre-existing CCHE panel connector options. The pigtailed cassettes have 900 µm at the connector panel for added durability and are colored 250 µm for ease of splicing. They also enable strain relief to be pre-applied to the assemblies from the manufacturing facility.

With the pigtailed cassette, individual splice tray or separate splice housings are eliminated, allowing splicing to be done away from the rack housing in more convenient workspaces. The modular design makes it easy to access the fibre in an individual cassette without disturbing the other fibres in the housing. Each cassette is shipped with the pigtailed CCHE adapter panel of the customer's choice, one rail for use with CCH-01U/2U/3U housings, and two rails used with CCH-04U housings. Grommets and cable ties for additional strain relief and protective braided tubing for incoming cable are also included. Splicing cassettes ship with the appropriate quantity and type of heat-shrink splice protectors.

## Features and Benefits

### **Manage cable slack for a CCH panel in a modular footprint**

Fast, easy and reliable initial routing, and quick, simple reaccess for moves, adds and changes (MACs)

### **Coloured 250 µm at splice point**

Easy to identify and prep coloured 250 µm for fast and easy splicing

### **Includes everything needed to convert a CCH housing for modular routing and/or splicing**

Easy ordering and field installation

### **Pre-prepped splice module**

Saves time in the field with a ready to splice product

### **Modular splice capability**

Manage all splices inside the housing

# CCHE Splice Module with Pigtails

CORNING

## Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

## Specifications

### General Specifications

Application	Data Centre , Enterprise Networks
Mounting Type	CCH Housings
Technology	Fusion Splice

### Temperature Range

Temperature range, operation	-40 °C - 65 °C
------------------------------	----------------

### Design

Part Number	Polish	Connector configuration	Number of pigtails	Housing type
CCHE-CS36-AF-P00RJ	APC	LC duplex	3	Cassettes
CCHE-CS12-AD-P00QE	PC	LC duplex	12	Cassettes
CCHE-CS24-AD-P00QE	PC	LC duplex	24	Cassettes
CCHE-CS12-AE-P00RE	UPC	LC duplex	12	Cassettes
CCHE-CS24-AE-P00RE	UPC	LC duplex	24	Cassettes
CCHE-CS36-AE-P00RJ	UPC	LC duplex	3	Cassettes

# CCHE Splice Module with Pigtails

CORNING

Design				
Part Number	Number of adapters	Number of ports	Number of splice protectors	Fibre count
CCHE-CS36-AF-P00RJ	18	36	3	36
CCHE-CS12-AD-P00QE	6	12	12	12
CCHE-CS24-AD-P00QE	12	24	24	24
CCHE-CS12-AE-P00RE	6	12	12	12
CCHE-CS24-AE-P00RE	12	24	24	24
CCHE-CS36-AE-P00RJ	18	36	3	36

Design		
Part Number	Panel or module type	Splice protectors type
CCHE-CS36-AF-P00RJ	CCHE	
CCHE-CS12-AD-P00QE	CCHE	Heat shrink splice protection
CCHE-CS24-AD-P00QE	CCHE	Heat shrink splice protection
CCHE-CS12-AE-P00RE	CCHE	Heat shrink splice protection
CCHE-CS24-AE-P00RE	CCHE	Heat shrink splice protection
CCHE-CS36-AE-P00RJ	CCHE	

Design Adapter		
Part Number	Adapter housing colour	Adapter type
CCHE-CS12-AE-P00RE	Blue	LC UPC Duplex Shuttered

# CCHE Splice Module with Pigtails

CORNING

## Design Adapter

Part Number	Adapter housing colour	Adapter type
CCHE-CS24-AE-P00RE	Blue	LC UPC Duplex Shuttered
CCHE-CS36-AE-P00RJ	Blue	LC UPC Duplex Shuttered
CCHE-CS36-AF-P00RJ	Green	LC APC Duplex Shuttered
CCHE-CS12-AD-P00QE	Turquoise	
CCHE-CS24-AD-P00QE	Turquoise	

## Dimension

Part Number	Width	Depth
CCHE-CS12-AD-P00QE	35 mm	200 mm
CCHE-CS12-AE-P00RE	35 mm	200 mm
CCHE-CS24-AD-P00QE	35 mm	200 mm
CCHE-CS24-AE-P00RE	35 mm	200 mm
CCHE-CS36-AE-P00RJ	35 mm	200 mm
CCHE-CS36-AF-P00RJ	35 mm	200 mm



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany  
+00 800 2675 4641 • FAX: +49 30 5303 2335 • [www.corning.com/opcomm/emea](http://www.corning.com/opcomm/emea)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/emea/trademarks](http://www.corning.com/opcomm/emea/trademarks). Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2024 Corning Optical Communications. All rights reserved.