

DualDrop™ Round Drop Cable with FastAccess™ Technology, A-VQH(ZN)2Y

CORNING

Corning DualDrop™ dielectric cable is a two-in-one cable uniquely designed for rugged outdoor and challenging indoor environments. The design features a gel-free, fully waterblocked, UV-resistant, 2.9 mm FRNC/LSZH drop cable centered inside a rugged outside plant drop cable. The cable features Fast Access™ Technology which enables long lengths of the inner subunit to be accessed in seconds simply by peeling away the outer jacket by hand. Designed to meet industry-standard requirements for outdoor and indoor drop cables, the product eliminates the need for termination hardware to transition from the outdoor environment to an indoor terminal. This dielectric cable eliminates any bonding and grounding requirements and is suitable for aerial, facade, direct buried and duct installation. Corning's ClearCurve® single-mode fiber inside the 2.9 mm subunit enables installers to route the subunit around tight corners down to 7.5 mm (0.3 in) radius inside the home.

Features and Benefits

Flexible, robust cable

Solves unique challenges associated with MDU deployments

Compact, robust design

Meets industry standards and eliminates installation complexity

2.9 mm FRNC/LSZH subunit in a rugged outdoor cable


Eliminates need for termination transition in indoor ONT

Small subunit diameter and bend-radius

Easy installation in space-constrained areas

Available in preconnectorized assemblies

Easy field installation and reduced labor costs



DualDrop™ Round Drop Cable with FastAccess™ Technology, A-VQH(ZN)2Y

DualDrop™ Round Drop Cable with FastAccess™ Technology, A-VQH(ZN)2Y

CORNING

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Specifications

General Specifications

Environment	Indoor/Outdoor
Product Type	Dielectric
Cable Type	Single Tube
Flame Rating	LSZH/FRNC
Reaction to Fire	Inner Subunit: Dca-s1a,d0,a1

Temperature Range

Temperature Range, Storage	-40 °C - 70 °C
Temperature Range, Installation	-5 °C - 50 °C
Temperature Range, Operation	-40 °C - 70 °C

Design Characteristics Cable

Fiber Count
1

Mechanical Characteristics Cable

Fiber Count	Max. Tensile Strength for Installation	Max. Tensile Strength, Long-Term	Cable Weight
1	1000 N	300 N	27 kg/km

DualDrop™ Round Drop Cable with FastAccess™ Technology, A-VQH(ZN)2Y

CORNING

Transmission Performance

Single-mode	
Fiber Name	ClearCurve® LBL - ClearCurve® ZBL
Performance Option Code	25
Fiber Category	OS2
Wavelengths	1310 nm / 1383 nm / 1550 nm
Fiber Code	J - U
Maximum Attenuation	0.38 dB/km / 0.38 dB/km / 0.25 dB/km



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
+00 800 2675 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2025 Corning Optical Communications. All rights reserved.