

EDGE™ Splice Cassette

The logo consists of a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

EDGE™ Splice Cassettes provide the interface between the bulk fiber cable and the LC duplex jumpers that connect directly into the electronics. The fiber splice cassette includes a one meter bare ribbon (or twelve x 250 μm single fiber) pigtail, that is loaded within the fiber splice cassette, and can be mass-fusion spliced directly to either ribbon or loose fiber cable. The LC duplex adapters feature hinged VFL-compatible shutters that move up and out of the way when the connector is inserted.

EDGE™ Splice Cassette



Specifications

General Specifications

Application	Data Center
Product Type	Cassettes
Splice option	Yes

Temperature Range

Temperature Range, Operation	-20 °C - 60 °C (-4 °F - 140 °F)
Temperature Range, Installation	-5 °C - 50 °C (23 °F - 122 °F)
Temperature Range, Storage	-25 °C - 70 °C (-13 °F - 158 °F)

Design

Part Number	Number of Splice Protectors	Fiber Count	Number of pigtails	Adapter Type Front
EDGE-CS12-AD-P00QE-CSP	12	12	12	Shuttered LC Duplex
EDGE-CS12-AD-P00QM-CSP	12	12	12	Shuttered LC Duplex
EDGE-CS12-AD-P00QU	12	12	12	Shuttered LC Duplex
EDGE-CS12-AE-P00RE	12	12	12	Shuttered LC Duplex
EDGE-CS12-AE-P00RM-CSP	12	12	12	Shuttered LC Duplex
EDGE-CS12-AF-P00RE	12	12	12	Shuttered LC Duplex
EDGE-CS12-AD-P00QJ		12		Shuttered LC Duplex
EDGE-CS12-AE-P00RJ		12		Shuttered LC Duplex

EDGE™ Splice Cassette



Design				
Part Number	Adapter Color Front	Number of Splice Trays	Pigtail Type	Splice Protectors Type
EDGE-CS12-AD-P00QE-CSP	Aqua	1	Telcordia color-coded for buffers and fibers	Crimp Splice Protection
EDGE-CS12-AD-P00QJ	Aqua			
EDGE-CS12-AD-P00QM-CSP	Aqua	1	Universal color-coded for buffers and fibers	Crimp Splice Protection
EDGE-CS12-AD-P00QU	Aqua	1	Universal color-coded for buffers and fibers	Heat Shrink Splice Protection
EDGE-CS12-AE-P00RE	Blue	1	Telcordia color-coded for buffers and fibers	Heat Shrink Splice Protection
EDGE-CS12-AE-P00RJ	Blue			
EDGE-CS12-AE-P00RM-CSP	Blue	1	Universal color-coded for buffers and fibers	Crimp Splice Protection
EDGE-CS12-AF-P00RE	Green	1	Telcordia color-coded for buffers and fibers	Heat Shrink Splice Protection

Design	
Part Number	Panel or Module Type
EDGE-CS12-AD-P00QE-CSP	EDGE
EDGE-CS12-AD-P00QJ	EDGE
EDGE-CS12-AD-P00QM-CSP	EDGE
EDGE-CS12-AD-P00QU	EDGE
EDGE-CS12-AE-P00RE	EDGE
EDGE-CS12-AE-P00RJ	EDGE

EDGE™ Splice Cassette



Design

Part Number	Panel or Module Type
EDGE-CS12-AE-P00RM-CSP	EDGE
EDGE-CS12-AF-P00RE	EDGE

Design Adapter

Part Number	Insert	Housing Material	Adapter Type
EDGE-CS12-AD-P00QE-CSP	Ceramic	Composite	LC
EDGE-CS12-AD-P00QJ	Ceramic	Composite	LC
EDGE-CS12-AD-P00QM-CSP	Ceramic	Composite	LC
EDGE-CS12-AD-P00QU	Ceramic	Composite	LC
EDGE-CS12-AE-P00RE	Ceramic	Composite	LC
EDGE-CS12-AE-P00RJ	Ceramic	Composite	LC
EDGE-CS12-AE-P00RM-CSP	Ceramic	Composite	LC
EDGE-CS12-AF-P00RE	Ceramic	Composite	LC

Ordering Information

Part Number	Units per Delivery
EDGE-CS12-AD-P00QE-CSP	1/1
EDGE-CS12-AD-P00QJ	1/1
EDGE-CS12-AD-P00QM-CSP	1/1
EDGE-CS12-AD-P00QU	1/1
EDGE-CS12-AE-P00RE	1/1
EDGE-CS12-AE-P00RJ	1/1
EDGE-CS12-AE-P00RM-CSP	1/1

EDGE™ Splice Cassette

The CORNING logo is displayed in white, uppercase letters on a dark blue rectangular background.

Part Number	Units per Delivery
EDGE-CS12-AF-P00RE	1/1



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.