

EDGE™ Tap Module

The Corning logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

EDGE Tap module for traditional LC duplex systems enables the customer to manage the monitoring access points via the patch cord infrastructure zone at the front of the cabinets. The Edge Tap Module enables passive optical tapping of the network while reducing downtime and link loss, and increasing rack space utilization and density.

Features and Benefits

Designed for Duplex based infrastructure solutions

Utilizes advanced splitter technology

Maintains equal modal power distribution, reducing insertion loss for increased link reach

EDGE Solutions-based footprint

Standards

RoHS	Free of hazardous substances according to RoHS 2011/65/EU
------	---

Specifications

General Specifications

Application	Data Center
Mounting Type	Rack-mount
Product Type	Modules

Design

Part Number	Adapter Type Front	Adapter Type Back	Fiber Count	Adapter Color Front
ETM-5C-G	MTP to MTP	MTP®	12	Black / Red
ETM-5C-Q	MTP to MTP	MTP®	12	Aqua / Red
ETM-7C-G	MTP to MTP	MTP®	12	Black / Red
ETM-7C-Q	MTP to MTP	MTP®	12	Aqua / Red
ETM-5C-G-R	MTP®	MTP®	12	Black
ETM-5C-Q-R	MTP®	MTP®	12	Aqua
ETM-7C-G-R	MTP®	MTP®	12	Black
ETM-7C-Q-R	MTP®	MTP®	12	Aqua
ETM-5A-G	Shuttered LC		4	Blue / Red
ETM-5A-G-DMX	Shuttered LC			Blue / Red
ETM-5A-Q	Shuttered LC		4	Aqua / Red
ETM-5B-G	Shuttered LC	MTP®	12	Blue
ETM-5B-G-S	Shuttered LC	MTP®		Blue
ETM-5B-Q	Shuttered LC	MTP®	12	Aqua
ETM-7A-G	Shuttered LC			Blue / Red
ETM-7A-G-DMX	Shuttered LC		4	Blue / Red
ETM-7A-Q	Shuttered LC		4	Aqua / Red

EDGE™ Tap Module

CORNING

Design				
Part Number	Adapter Type Front	Adapter Type Back	Fiber Count	Adapter Color Front
ETM-7B-G	Shuttered LC	MTP®	12	Blue
ETM-7B-G-S	Shuttered LC	MTP®	12	Blue
ETM-7B-Q	Shuttered LC	MTP®	12	Aqua
ETM-7B-Q-S	Shuttered LC	MTP®	12	Aqua

Design				
Part Number	Number of Ports	Housing Type	Adapter Color Back	Panel or Module Type
ETM-5C-G		Modules	Black	
ETM-5C-Q		Modules	Aqua	EDGE™
ETM-7C-G		Modules	Black	
ETM-7C-Q		Modules	Aqua	EDGE™
ETM-5C-G-R		Modules	Black / Red	
ETM-5C-Q-R		Modules	Aqua / Red	
ETM-7C-G-R		Modules	Black / Red	
ETM-7C-Q-R		Modules	Aqua / Red	
ETM-5A-G	4	Modules		
ETM-5A-G-DMX	4	Modules		
ETM-5A-Q	4	Modules		
ETM-5B-G	12	Modules	Black / Red	
ETM-5B-G-S	12	Modules	Black / Red	
ETM-5B-Q	6	Modules	Aqua / Red	
ETM-7A-G	2	Modules		
ETM-7A-G-DMX	1	Modules		
ETM-7A-Q		Modules		
ETM-7B-G		Modules	Black / Red	
ETM-7B-G-S		Modules	Black / Red	
ETM-7B-Q		Modules	Aqua / Red	
ETM-7B-Q-S		Modules	Aqua / Red	

EDGE™ Tap Module

CORNING

Dimension			
Part Number	Height	Depth	Width
ETM-7A-G-DMX			152 mm
ETM-5A-G	12 mm	152 mm	191 mm
ETM-5A-G-DMX		152 mm	191 mm
ETM-5A-Q	12 mm	152 mm	115 mm
ETM-5B-G	12 mm	165 mm	90 mm
ETM-5B-Q	12 mm	165 mm	90 mm
ETM-5C-G	12 mm	159 mm	217 mm
ETM-5C-G-R	12 mm	159 mm	242 mm
ETM-5C-Q	12 mm	159 mm	140 mm
ETM-7A-Q	12 mm	152 mm	267 mm
ETM-7B-G	12 mm	165 mm	90 mm
ETM-7B-G-S		165 mm	496 mm
ETM-7C-G	12 mm	159 mm	369 mm
ETM-7C-G-R	12 mm	159 mm	394 mm
ETM-7C-Q	12 mm	159 mm	293 mm
ETM-7C-Q-R	12 mm	159 mm	318 mm
ETM-5C-Q-R	13 mm	159 mm	166 mm
ETM-7A-G	14 mm	152 mm	344 mm
ETM-7B-Q	15 mm	165 mm	90 mm

Ordering Information

Part Number	Units per Delivery
ETM-5A-G	1/1
ETM-5A-G-DMX	1/1
ETM-5A-Q	1/1
ETM-5B-G	1/1
ETM-5B-G-S	1/1

EDGE™ Tap Module

CORNING

Part Number	Units per Delivery
ETM-5B-Q	1/1
ETM-5C-G	1/1
ETM-5C-G-R	1/1
ETM-5C-Q	1/1
ETM-5C-Q-R	1/1
ETM-7A-G	1/1
ETM-7A-G-DMX	1/1
ETM-7A-Q	1/1
ETM-7B-G	1/1
ETM-7B-G-S	1/1
ETM-7B-Q	1/1
ETM-7B-Q-S	1/1
ETM-7C-G	1/1
ETM-7C-G-R	1/1
ETM-7C-Q	1/1
ETM-7C-Q-R	1/1



Corning Optical Communications GmbH & Co. KG • Leipziger Strasse 121 • 10117 Berlin, Germany
00 800 2676 4641 • FAX: • www.corning.com/opcomm/emea

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.