

EDGE™ Tap Module

The Corning logo is a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

EDGE Tap module for traditional LC duplex systems enables the customer to manage the monitoring access points via the patch cord infrastructure zone at the front of the cabinets. The Edge Tap Module enables passive optical tapping of the network while reducing downtime and link loss, and increasing rack space utilization and density.

Features and Benefits

Designed for Duplex based infrastructure solutions

Utilizes advanced splitter technology

Maintains equal modal power distribution, reducing insertion loss for increased link reach

EDGE Solutions-based footprint

Standards

RoHS

Free of hazardous substances according to RoHS 2011/65/EU

Specifications

General Specifications

Application

Data Center

Mounting Type

Rack-mount

Design

Part Number	Adapter Type Front	Adapter Type Back	Fiber Count	Adapter Color Front
ETM-5C-G	MTP to MTP	MTP®	12	Black / Red
ETM-5C-Q	MTP to MTP	MTP®	12	Aqua / Red
ETM-7C-G	MTP to MTP	MTP®	12	Black / Red
ETM-7C-Q	MTP to MTP	MTP®	12	Aqua / Red
ETM-5C-G-R	MTP®	MTP®	12	Black
ETM-5C-Q-R	MTP®	MTP®	12	Aqua
ETM-7C-G-R	MTP®	MTP®	12	Black
ETM-7C-Q-2X3	MTP®	MTP®	24	Aqua / Red
ETM-7C-Q-R	MTP®	MTP®	12	Aqua
ETM-5A-G	Shuttered LC		4	Blue / Red
ETM-5A-G-DMX	Shuttered LC			Blue / Red
ETM-5A-Q	Shuttered LC		4	Aqua / Red
ETM-5B-G	Shuttered LC	MTP®	12	Blue
ETM-5B-G-S	Shuttered LC	MTP®		Blue
ETM-5B-Q	Shuttered LC	MTP®	12	Aqua
ETM-7A-G	Shuttered LC			Blue / Red
ETM-7A-G-DMX	Shuttered LC		4	Blue / Red
ETM-7A-Q	Shuttered LC		4	Aqua / Red

EDGE™ Tap Module

CORNING

Design				
Part Number	Adapter Type Front	Adapter Type Back	Fiber Count	Adapter Color Front
ETM-7B-G	Shuttered LC	MTP®	12	Blue
ETM-7B-G-S	Shuttered LC	MTP®	12	Blue
ETM-7B-Q	Shuttered LC	MTP®	12	Aqua
ETM-7B-Q-S	Shuttered LC	MTP®	12	Aqua

Design				
Part Number	Number of Ports	Housing Type	Adapter Color Back	Panel or Module Type
ETM-5C-G		Modules	Black	
ETM-5C-Q		Modules	Aqua	EDGE™
ETM-7C-G		Modules	Black	
ETM-7C-Q		Modules	Aqua	EDGE™
ETM-5C-G-R		Modules	Black / Red	
ETM-5C-Q-R		Modules	Aqua / Red	
ETM-7C-G-R		Modules	Black / Red	
ETM-7C-Q-2X3		Modules	Aqua	
ETM-7C-Q-R		Modules	Aqua / Red	
ETM-5A-G	4	Modules		
ETM-5A-G-DMX	4	Modules		
ETM-5A-Q	4	Modules		
ETM-5B-G	12	Modules	Black / Red	
ETM-5B-G-S	12	Modules	Black / Red	
ETM-5B-Q	6	Modules	Aqua / Red	
ETM-7A-G	2	Modules		
ETM-7A-G-DMX	1	Modules		
ETM-7A-Q		Modules		
ETM-7B-G		Modules	Black / Red	
ETM-7B-G-S		Modules	Black / Red	
ETM-7B-Q		Modules	Aqua / Red	

EDGE™ Tap Module

CORNING

Design

Part Number	Number of Ports	Housing Type	Adapter Color Back	Panel or Module Type
ETM-7B-Q-S		Modules	Aqua / Red	

Dimension

Part Number	Height	Depth	Width
ETM-7A-G-DMX			152 mm (5.98 in)
ETM-5A-G	12 mm (0.47 in)	152 mm (5.98 in)	191 mm (7.52 in)
ETM-5A-G-DMX		152 mm (5.98 in)	191 mm (7.52 in)
ETM-5A-Q	12 mm (0.47 in)	152 mm (5.98 in)	115 mm (4.53 in)
ETM-5B-G	12 mm (0.47 in)	165 mm (6.5 in)	90 mm (3.54 in)
ETM-5B-Q	12 mm (0.47 in)	165 mm (6.5 in)	90 mm (3.54 in)
ETM-5C-G	12 mm (0.47 in)	159 mm (6.26 in)	217 mm (8.54 in)
ETM-5C-G-R	12 mm (0.47 in)	159 mm (6.26 in)	242 mm (9.53 in)
ETM-5C-Q	12 mm (0.47 in)	159 mm (6.26 in)	140 mm (5.51 in)
ETM-7A-Q	12 mm (0.47 in)	152 mm (5.98 in)	267 mm (10.51 in)
ETM-7B-G	12 mm (0.47 in)	165 mm (6.5 in)	90 mm (3.54 in)
ETM-7B-G-S		165 mm (6.5 in)	496 mm (19.53 in)
ETM-7C-G	12 mm (0.47 in)	159 mm (6.26 in)	369 mm (14.53 in)
ETM-7C-G-R	12 mm (0.47 in)	159 mm (6.26 in)	394 mm (15.51 in)
ETM-7C-Q	12 mm (0.47 in)	159 mm (6.26 in)	293 mm (11.54 in)
ETM-7C-Q-2X3	12 mm (0.47 in)	144.3 mm (5.68 in)	90 mm (3.54 in)
ETM-7C-Q-R	12 mm (0.47 in)	159 mm (6.26 in)	318 mm (12.52 in)
ETM-5C-Q-R	13 mm (0.51 in)	159 mm (6.26 in)	166 mm (6.54 in)
ETM-7A-G	14 mm (0.55 in)	152 mm (5.98 in)	344 mm (13.54 in)
ETM-7B-Q	15 mm (0.59 in)	165 mm (6.5 in)	90 mm (3.54 in)

Ordering Information

Part Number	Units per Delivery
ETM-5A-G	1/1
ETM-5A-G-DMX	1/1
ETM-5A-Q	1/1
ETM-5B-G	1/1
ETM-5B-G-S	1/1
ETM-5B-Q	1/1
ETM-5C-G	1/1
ETM-5C-G-R	1/1
ETM-5C-Q	1/1
ETM-5C-Q-R	1/1
ETM-7A-G	1/1
ETM-7A-G-DMX	1/1
ETM-7A-Q	1/1
ETM-7B-G	1/1
ETM-7B-G-S	1/1
ETM-7B-Q	1/1
ETM-7B-Q-S	1/1
ETM-7C-G	1/1
ETM-7C-G-R	1/1
ETM-7C-Q	1/1
ETM-7C-Q-2X3	1/1
ETM-7C-Q-R	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2026 Corning Optical Communications. All rights reserved.