

EDGE8® Tap Harness

The Corning logo consists of a solid blue square. Inside the square, the word "CORNING" is written in a white, serif, all-caps font, centered horizontally and vertically.

EDGE8® MTP® PRO to MTP PRO tap harness is used to break out the 8-fiber tap port at the rear of the EDGE8 tap module into two 4-fiber MTP PRO connectors that plug into monitoring electronics.

EDGE8® Tap Harness



Standards	
RoHS	Free of hazardous substances according to RoHS 2011/65/EU

Temperature Range	
Temperature Range, Operation	-10 °C - 60 °C (14 °F - 140 °F)

Design		
Part Number	Fiber Count	Outer Jacket Material
HE50308QPH-KB010F	8	Plenum
HE5E608QPH-KB010F	8	Plenum
HE70208GPH-KB010F	8	Plenum

Specifications - Connector A			
Connector Type	Boot Type	Boot Color	Ferrule Material
MTP® PRO (pinned)	Individual	Black	Composite

Specifications - Connector B				
Connector Type	Ferrule Material	Boot Color	Connector Type	Ferrule Material
LC	Ceramic	Black	MTP® PRO (pinned)	Composite
MTP® PRO (non-pinned)	Composite	Black	MTP® PRO (pinned)	Composite
LC	Ceramic	Black	MTP® PRO (pinned)	Composite

Mechanical Characteristics		
Part Number	Min. Bend Radius Installation	Min. Bend Radius Operation
HE50308QPH-KB010F	30 mm (1.18 in)	10 mm (0.39 in)
HE5E608QPH-KB010F	30 mm (1.18 in)	10 mm (0.39 in)

EDGE8® Tap Harness



Mechanical Characteristics		
Part Number	Min. Bend Radius Installation	Min. Bend Radius Operation
HE70208GPH-KB010F	30 mm (1.18 in)	10 mm (0.39 in)

Furcation A				
Furcation Type	Leg Color	Leg Length	Leg Diameter	Leg Length non-unit
EDGE™ Harness Plug	Aqua	600 mm -0/+76.2mm -0/+3in (23.62 in -0/+76.2mm -0/+3in)	2 mm	Non-staggered (600 mm/24 in)
EDGE™ Harness Plug	Aqua - Yellow	600 mm -0/+76.2mm -0/+3in (23.62 in -0/+76.2mm -0/+3in)	2 mm	



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2024 Corning Optical Communications. All rights reserved.