

EDGE™ Tap Module

The Corning logo is a dark blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

EDGE Tap module for traditional LC duplex systems enables the customer to manage the monitoring access points via the patch cord infrastructure zone at the front of the cabinets.

Features and Benefits

Designed for Duplex based infrastructure solutions

Utilizes advanced splitter technology

Maintains equal modal power distribution, reducing insertion loss for increased link reach

EDGE Solutions-based footprint

RoHS	
RoHS 2011/65/EU	

Specifications

Design				
Part Number				
ETM-5C-G-R	MTP®	MTP®	12	
ETM-5C-Q-R	MTP®	MTP®	12	
ETM-7C-G-R	MTP®	MTP®	12	
ETM-7C-Q-R	MTP®	MTP®	12	
ETM-5C-G	MTP® / MTP	MTP®	12	
ETM-5C-Q	MTP® / MTP	MTP®	12	
ETM-7C-G	MTP® / MTP	MTP®	12	
ETM-7C-Q	MTP® / MTP	MTP®	12	
ETM-5A-G	LC		4	
ETM-5A-G-DMX	LC			
ETM-5A-Q	LC		4	
ETM-5B-G	LC	MTP®	12	
ETM-5B-G-S	LC	MTP®		
ETM-5B-Q	LC	MTP®	12	
ETM-7A-G	LC			
ETM-7A-G-DMX	LC		4	
ETM-7A-Q	LC		4	



Design				
Part Number	□□□□□□□	□□□□□□□	□□□□	□□□□□□□
ETM-7B-G	□□□□□□LC	MTP®	12	□□
ETM-7B-G-S	□□□□□□LC	MTP®	12	□□
ETM-7B-Q	□□□□□□LC	MTP®	12	□□□
ETM-7B-Q-S	□□□□□□LC	MTP®	12	□□□

Design				
Part Number	□□□	□□□□□	□□□□□□□	□□□□□□□
ETM-5C-G-R		□□	□□ / □□	
ETM-5C-Q-R		□□	□□□ / □□	
ETM-7C-G-R		□□	□□ / □□	
ETM-7C-Q-R		□□	□□□ / □□	
ETM-5C-G		□□	□□	
ETM-5C-Q		□□	□□□	EDGE™
ETM-7C-G		□□	□□	
ETM-7C-Q		□□	□□□	EDGE™
ETM-5A-G	4	□□		
ETM-5A-G-DMX	4	□□		
ETM-5A-Q	4	□□		
ETM-5B-G	12	□□	□□ / □□	
ETM-5B-G-S	12	□□	□□ / □□	
ETM-5B-Q	6	□□	□□□ / □□	
ETM-7A-G	2	□□		
ETM-7A-G-DMX	1	□□		
ETM-7A-Q		□□		
ETM-7B-G		□□	□□ / □□	
ETM-7B-G-S		□□	□□ / □□	
ETM-7B-Q		□□	□□□ / □□	
ETM-7B-Q-S		□□	□□□ / □□	



Dimension			
Part Number	◇◇	◇◇	◇◇
ETM-7A-G-DMX			152 mm
ETM-5A-G	12 mm	152 mm	191 mm
ETM-5A-G-DMX		152 mm	191 mm
ETM-5A-Q	12 mm	152 mm	115 mm
ETM-5B-G	12 mm	165 mm	90 mm
ETM-5B-Q	12 mm	165 mm	90 mm
ETM-5C-G	12 mm	159 mm	217 mm
ETM-5C-G-R	12 mm	159 mm	242 mm
ETM-5C-Q	12 mm	159 mm	140 mm
ETM-7A-Q	12 mm	152 mm	267 mm
ETM-7B-G	12 mm	165 mm	90 mm
ETM-7B-G-S		165 mm	496 mm
ETM-7C-G	12 mm	159 mm	369 mm
ETM-7C-G-R	12 mm	159 mm	394 mm
ETM-7C-Q	12 mm	159 mm	293 mm
ETM-7C-Q-R	12 mm	159 mm	318 mm
ETM-5C-Q-R	13 mm	159 mm	166 mm
ETM-7A-G	14 mm	152 mm	344 mm
ETM-7B-Q	15 mm	165 mm	90 mm

Ordering Information

Part Number	◇◇◇◇◇◇◇◇
ETM-5A-G	1/1
ETM-5A-G-DMX	1/1
ETM-5A-Q	1/1
ETM-5B-G	1/1
ETM-5B-G-S	1/1

EDGE™ Tap Module



Part Number	◇◇◇◇◇◇◇◇
ETM-5B-Q	1/1
ETM-5C-G	1/1
ETM-5C-G-R	1/1
ETM-5C-Q	1/1
ETM-5C-Q-R	1/1
ETM-7A-G	1/1
ETM-7A-G-DMX	1/1
ETM-7A-Q	1/1
ETM-7B-G	1/1
ETM-7B-G-S	1/1
ETM-7B-Q	1/1
ETM-7B-Q-S	1/1
ETM-7C-G	1/1
ETM-7C-G-R	1/1
ETM-7C-Q	1/1
ETM-7C-Q-R	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • ◇◇
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.