

Evolv™ ROC™ Drop Assembly

The Corning logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font.

As an industry leader in optical connectivity products, Corning designs and manufactures the ROC™ drop cable assembly with factory-terminated, environmentally sealed and hardened connectors to reduce the cost and time of drop cable deployment. The Corning hardened connector provides superior durability and reliability in the drop segment of the network. This assembly also offers significant improvements in cable management.

By featuring the ROC drop cable design, issues of slack storage capacity are virtually eliminated. The ROC drop cable minimum bend radius is half the size of legacy drop cable. The outer dimensions of the cable have been reduced by more than 50 percent. ROC drop cables are more flexible, allowing for easier routing at the ONT. Installers will see a reduction in truck storage space requirements with this new design.

Features and Benefits

Hardened connector technology

Reduced-diameter Pushlok™ connector

Reduced optimized cable cross-section

Smaller profile and bend radius, flexibility allows for increased slack storage capacity in existing optical network terminals (ONTs), pedestals and handholes

Robust design

Designed for rapid connection to external flush-mounted bulkhead adapters on terminals or closures

Flexible connector offerings

Dual-ended or pigtailed versions to accommodate any ONT interface; hybrid assemblies with hardened connector (terminal) to SC APC (ONT)

Versatile installation environments

Aerial: dielectric, self-supporting at 40 lbs installation tension at 150 ft (NESC Heavy), 255 ft (NESC Medium) or 330 ft (NESC Light) Direct-buried: toneable for easy locating Duct: integral pulling eye/connector cap designed for 100 lb maximum pulling tension; Pushlok connector is suitable for 13 mm inner diameter duct

Evolv™ ROC™ Drop Assembly

CORNING

标准

RoHS

无有害物质根据RoHS 2011/65/EU

Temperature Range

温度范围，操作

-40 °C - 70 °C (-40 F - 158 F)

Specifications - Connector A

连接器类型	插入损耗，典型	反射，典型的
Pushlok	≤ 0.15 dB	> 65 dB (光回损)
尾纤	≤ 0.15 dB	

Specifications - Connector B

连接器类型	反射，典型的	插入损耗，典型	连接器类型
Pushlok		≤ 0.15 dB	尾纤
SC单工	> 65 dB (光回损)	≤ 0.15 dB	Pushlok
Pushlok	> 65 dB (光回损)	≤ 0.15 dB	Pushlok

Mechanical Characteristics

Part Number	轴向拉伸，接头到缆，通过防尘盖	冷插拔	Cable Length
00D101EB49R030M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	30 m
00D101EB49R100M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	100 m
00D101EB49R100M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	100 m
00D101EB49R200M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	200 m
00D101EB49R200M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	200 m

Evolv™ ROC™ Drop Assembly

CORNING

Mechanical Characteristics			
Part Number	轴向拉伸，接头到缆，通过防尘盖	冷插拔	Cable Length
00D101EB49R300M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	300 m
00D101EB49R300M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	300 m
00D101JB49R030M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	30 m
D14401EB49R300M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	300 m
D14401EB49R300M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	300 m
D14401EB4R3030M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	30 m
D14401EB4R3030M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	30 m
D14401EB4R3100M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	100 m
D14401EB4R3100M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	100 m
D14401EB4R3200M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	200 m
D14401EB4R3200M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	200 m
D1D101EB49R030M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	30 m
D1D101EB49R030M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	30 m
D1D101EB49R100M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	100 m
D1D101EB49R100M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	100 m
D1D101EB49R200M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	200 m
D1D101EB49R200M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	200 m

Evolv™ ROC™ Drop Assembly

CORNING

Mechanical Characteristics			
Part Number	轴向拉伸，接头到缆，通过防尘盖	冷插拔	Cable Length
D1D101EB49R300M	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	300 m
D1D101EB49R300M-P	444.82 N (100 磅) 轴向拉力，并将负载施加到防尘盖上	-40 °C (-40 F)	300 m

Ordering Information

Part Number	每次交付的单元数
00D101EB49R030M-P	1/1
00D101EB49R100M-P	1/1
00D101EB49R200M-P	1/1
00D101EB49R300M-P	1/1
D14401EB49R300M-P	1/1
D14401EB4R3030M-P	1/1
D14401EB4R3100M-P	1/1
D14401EB4R3200M-P	1/1
D1D101EB49R030M-P	1/1
D1D101EB49R100M-P	1/1
D1D101EB49R200M-P	1/1
D1D101EB49R300M-P	1/1
00D101EB49R200M	10/1
D1D101EB49R200M	10/1
00D101EB49R100M	20/1
D14401EB49R300M	20/1
D14401EB4R3200M	20/1
D1D101EB49R100M	20/1
00D101JB49R030M	50/1
D14401EB4R3030M	50/1

Evolv™ ROC™ Drop Assembly

CORNING

Part Number	每次交付的单元数
D14401EB4R3100M	50/1
D1D101EB49R030M	50/1
00D101EB49R300M	6/1
D1D101EB49R300M	6/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • 美国
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2022 Corning Optical Communications. All rights reserved.