

Everon™ Copper Datacom E250 Flex

CORNING

Our Cat.6 copper interconnect products work together to provide an easy-to-use solution for deploying high-speed connections throughout a building. The RJ45 jack is a key component in this system. The jack's unique two cable entry points help make installation simple. The traditional one-click design enables an easy, tool-less termination on unshielded twisted pair cables, meeting industry performance standards.

Features and Benefits

Tool-less jack

Easy and quick to install - reliable connection
The conductors are wired in a single operation

Two cable entry points

Less cable bending required - better compliance with minimum bend radius
Enables a wide range of cable routing options
Easy to use in tight spaces

Reusable

Jack can be reused even after wiring mistake

Clip-in mounting

Designed to fit many other accessories

Accepts solid and stranded conductors

Enables "jack-to-plug" cables to be manufactured using stranded conductors

Integral shutter

No additional shuttering required on faceplates

No untwisting of pairs before termination

Minimized stripping length - limited pair untwist - pairs kept together, no wire guide required

PoE Applications

Supports Power over Ethernet (PoE / PoE+)

Everon™ Copper Datacom E250 Flex

CORNING

Specifications

General Specifications

Category	6
----------	---

Environmental Conditions

Temperature Range, Operation	-10 °C - 60 °C (14 F - 140 F)
------------------------------	-------------------------------

Design

Part Number	Insulation diameter max.	Jack Type	Color	Housing Material	Conductor
UU001520574	1.6 mm	RJ45 - 8/8	White	Plastic	26 - 22 AWG
UU001520582	1.6 mm	RJ45 - 8/8	White	Plastic	26 - 22 AWG

Mechanical Characteristics

Part Number	Contact surface
UU001520574	Gold, 1.6 µm
UU001520582	Gold, 1.6 µm

Ordering Information

Part Number	Units per Delivery
UU001520582	480/1
UU001520574	96/1

Everon™ Copper Datacom E250 Flex

The Corning logo consists of the word "CORNING" in a white, serif, all-caps font, centered within a solid blue square.

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2022 Corning Optical Communications. All rights reserved.