

# Everon® Copper Datacom V250 Unshielded

CORNING

Our Cat.6 copper interconnect products work together to provide an easy-to-use solution for deploying high-speed connections throughout a building. The RJ45 jack is a key component in this system. These RJ45 jacks have been certified by an independent test laboratory to hardware certification. Each jack component is able to terminate to any certified Cat.6 TIA, ISO/IEC and EN standards for hardware performance, confirmed by independent laboratory certifications. The jack's unique three cable entry points help make installation simple. The traditional one-click design enables an easy, tool-less termination on Cat. 6 unshielded twisted pair cables, meeting industry performance standards.

## Características e benefícios

### **Tool-less jack**

Easy and quick to install - reliable connection  
The conductors are wired in a single operation

### **Three cable entry points**

Less cable bending required - better compliance with minimum bend radius

### **No untwisting of pairs before termination**

Minimized stripping length - limited pair untwist - pairs kept together, no wire guide required

### **Accepts solid and stranded conductors**

Enables "jack-to-plug" cables to be manufactured using stranded conductors

### **Accepts solid and stranded conductors**

Enables "jack-to-plug" cables to be manufactured using stranded conductors

### **Hardware Performance**

Can be mixed and matched with other Hardware certified copper cable and patchcords

Tested and approved for Power over Ethernet applications (PoE/PoE+/4PPoE) according to IEEE 802.3af, IEEE 802.3at and IEEE 802.3bt up to 90W



| Normas |                                                              |
|--------|--------------------------------------------------------------|
| RoHS   | Livre de substâncias perigosas de acordo com RoHS 2011/65/EU |

Specifications

| Especificações gerais |   |
|-----------------------|---|
| Categoria             | 6 |

| Design      |                             |              |          |                     |           |
|-------------|-----------------------------|--------------|----------|---------------------|-----------|
| Part Number | Diâmetro de isolamento máx. | Tipo de jack | Cor      | Material da carcaça | Condutor  |
| XF500006309 | 1,6 mm                      | RJ45 - 8/8   | Azul     | Plástico            | AWG 24-22 |
| XF500006317 | 1,6 mm                      | RJ45 - 8/8   | Verde    | Plástico            | AWG 24-22 |
| XF500006325 | 1,6 mm                      | RJ45 - 8/8   | Vermelho | Plástico            | AWG 24-22 |
| XF500006333 | 1,6 mm                      | RJ45 - 8/8   | Amarelo  | Plástico            | AWG 24-22 |
| XF500006341 | 1,6 mm                      | RJ45 - 8/8   | Preto    | Plástico            | AWG 24-22 |
| XF500006424 | 1,6 mm                      | RJ45 - 8/8   | Branco   | Plástico            | AWG 24-22 |
| XF500006432 | 1,6 mm                      | RJ45 - 8/8   | Branco   | Plástico            | AWG 24-22 |

| Mechanical Characteristics |                       |
|----------------------------|-----------------------|
| Part Number                | Superfície de contato |
| XF500006309                | Dourado, 1,27 µm      |
| XF500006317                | Dourado, 1,27 µm      |
| XF500006325                | Dourado, 1,27 µm      |

# Everon® Copper Datacom V250 Unshielded

CORNING

| Mechanical Characteristics |                       |
|----------------------------|-----------------------|
| Part Number                | Superfície de contato |
| XF500006333                | Dourado, 1,27 µm      |
| XF500006341                | Dourado, 1,27 µm      |
| XF500006424                | Dourado, 1,27 µm      |
| XF500006432                | Dourado, 1,27 µm      |



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil  
+55 21 3416 5150 • FAX: +55 21 2441 2037 • [www.corning.com/opcomm/csa](http://www.corning.com/opcomm/csa)

Uma lista completa das marcas registrada da Corning Comunicações Ópticas está disponível em [www.corning.com/opcomm/trademarks](http://www.corning.com/opcomm/trademarks). Todas as outras marcas são de propriedade de seus respectivos proprietários. Corning Comunicações Ópticas é certificada ISO 9001. ©2024 Corning Comunicações Ópticas. Todos os direitos reservados.