

Everon® Copper Datacom V500S Shielded



The Everon® Copper Datacom V500s module offers high system margins for transmission of digital data signals for future applications in systems up to 10GbE according to the new class EA (ISO/IEC 11801 respectively Cat.6A (ANSI/TIA/EIA 568B.2-10), EN 50173 and IEC 60603-7-51 (IEC48B/1977/CDV). The module is also suitable for Power over Ethernet (PoE) applications in compliance with IEEE 802.3af and the new PoE Plus applications. No special tools are required for either the termination of modules onto cables or the installation of the modules into outlets. The individual single shielding of the modules (in compliance to EN 50174) is absolutely necessary for these high-bit-rate applications.

Características e benefícios

- Fulfil the requirements for the 2and 3connector model according to EA Class
- 3-Connector Permanent Link / Channel
- Suitable for EA Class applications according to ISO/IEC 11801
- Universal application in all modular VOL components
- Quick and easy to install (compact design, only 3 individual components, no specific tools required)
- Individual jack shielding by stable diecast housing
- 360° shield contact and cable strain-relief without cable tie
- Captive dust cover
- All components are certified as Category 6A according to ISO/IEC 11801
- Certified by a vendor-independent and impartial test lab (GHMT AG); PVP Certificate
- Tested and approved for Power over Ethernet applications (PoE/PoE+/4PPoE) according to IEEE 802.3af, IEEE 802.3at and IEEE 802.3bt up to 90W

Everon® Copper Datacom V500S Shielded



Normas	
RoHS	Livre de substâncias perigosas de acordo com RoHS 2011/65/EU

Specifications

Especificações gerais	
Categoria	6A

Environmental Conditions	
Faixa de temperatura, operação	-10 °C - 60 °C (14 °F - 140 °F)

Design					
Part Number	Diâmetro de isolamento máx.	Tipo de jack	Cor	Material da carcaça	Condutor
XF500003546	1,6 mm	RJ45 - 8/8	Branco	Metal	AWG 24-22
XF500003553	1,6 mm	RJ45 - 8/8	Branco	Metal	AWG 24-22

Mechanical Characteristics	
Part Number	Superfície de contato
XF500003546	Dourado, 1,27 µm
XF500003553	Dourado, 1,27 µm

Everon® Copper Datacom V500S Shielded

CORNING



Corning Comunicacoes Opticas • Estrada do Camorim 633 • Jacarepagua CEP 22780-070 • Rio De Janeiro, RJ Brazil
+55 21 3416 5150 • FAX: +55 21 2441 2037 • www.corning.com/opcomm/csa

Uma lista completa das marcas registrada da Corning Comunicações Ópticas está disponível em www.corning.com/opcomm/trademarks. Todas as outras marcas são de propriedade de seus respectivos proprietários. Corning Comunicações Ópticas é certificada ISO 9001. ©2024 Corning Comunicações Ópticas. Todos os direitos reservados.