

Small Wall Terminal (SWT)

The Corning logo is a solid blue square with the word "CORNING" in white, uppercase, sans-serif font centered within it.

CORNING

The small wall terminal is specifically designed to be installed close to or inside the subscriber premises. The terminal is suitable for FTTH applications in both multidwelling units (MDU) and single-family units (SFU). It provides an interface between the installed network and the customer device (ONT). The outlet is designed to be easily installed by operators, and its compact design is suitable for use in the home. The terminal can accommodate field-installable connectors or preconnectorized cables. Empty terminals can hold up to 9 m of slack for a 3 mm jacketed cable and can hold up to 4 SC adapters or 8 LC adapters.

Small Wall Terminal (SWT)



RoHS		RoHS 2011/65/EU
------	--	-----------------

Specifications

Design				
Part Number				
SWT4-1-5C000-SF0BW-S	1		1	
SWT4-1-6C000-SB0KW-S	1		1	
SWT4-1-6C000-SF0BW-S	1		1	
SWT4-1-6C44H-SB3KW-S	1		1	
SWT4-1-6W000-SB0KW-S	1		1	
SWT4-1-6W000-SB3KW-S	1		1	
SWT4-1-6W44H-SB3KW-S	1		1	
SWT4-2-6C000-SB0KW-S	2		2	
SWT4-2-6C000-SB3KW-S	2		2	
SWT4-2-6C000-SF0BW-S	2		2	

Small Wall Terminal (SWT)

CORNING

Design				
Part Number	□□□□	□□□□□□	□□□□	□□□□□
SWT4-2-6C000-SF3BW-S	2	□□□, □□□□□	2	□□
SWT4-2-6C44H-SB3KW-S	2	□□□, □□□□□	2	□□
SWT4-2-6S000-SF0BW-S	2	□□□, □□□□□	2	□□
SWT4-2-6S44H-SB3KW-S	2	□□□, □□□□□	2	□□
SWT4-2-6W000-SB3KW-S	2	□□□, □□□□□	2	□□
SWT4-2-6W000-SF3BW-S	2	□□□, □□□□□	2	□□
SWT4-2-6W44H-SB3KW-S	2	□□□, □□□□□	2	□□
SWT4-4-04000-SF0BW-S	4	□□□, □□□□□	2	□□
SWT4-4-5C000-SF0BW-S	4	□□□, □□□□□	4	□□
SWT4-4-6C000-SB0KW-S	4	□□□, □□□□□	4	□□
SWT4-4-6S44H-SB3KW-S	4	□□□, □□□□□	4	□□
SWT4-4-6W000-SB3KW-S	4	□□□, □□□□□	4	□□
SWT4-4-BS000-SB3KW-S	4	□□□, □□□□□	2	□□
SWT4-8-B3000-SB3KW-S	8	□□□, □□□□□	4	□□

Design				
Part Number	□□□	□□□□	□□□□□	□□□□□
SWT4-1-6C44H-SB3KW-S	1	1	□□□□□	□□□□□□□□□□ □□□□□□□□
SWT4-1-6W44H-SB3KW-S	1	1	□□□□□	□□□□□□□□□□ □□□□□□□□

Small Wall Terminal (SWT)

CORNING

Design				
Part Number	◇◇◇	◇◇◇◇	◇◇◇◇◇	◇◇◇◇◇
SWT4-2-6C44H-SB3KW-S	2	1	◇◇◇◇◇	◇◇◇◇◇◇◇◇◇◇◇◇◇◇ ◇◇◇◇◇◇◇◇
SWT4-2-6S44H-SB3KW-S	2	1	◇◇◇◇◇◇	◇◇◇◇◇◇◇◇◇◇◇◇◇◇ ◇◇◇◇◇◇◇◇◇
SWT4-2-6W44H-SB3KW-S	2	1	◇◇◇◇◇◇	◇◇◇◇◇◇◇◇◇◇◇◇◇◇ ◇◇◇◇◇◇◇◇◇
SWT4-4-6S44H-SB3KW-S	4	1	◇◇◇◇◇◇	◇◇◇◇◇◇◇◇◇◇◇◇◇◇ ◇◇◇◇◇◇◇◇◇◇
SWT4-1-6W000-SB3KW-S		1	◇◇◇◇◇◇	
SWT4-2-6C000-SB3KW-S		1	◇◇◇◇◇◇	
SWT4-2-6C000-SF3BW-S		1	◇◇◇◇◇◇	
SWT4-2-6W000-SB3KW-S		1	◇◇◇◇◇◇	
SWT4-2-6W000-SF3BW-S		1	◇◇◇◇◇◇	
SWT4-4-6W000-SB3KW-S		1	◇◇◇◇◇◇	
SWT4-4-BS000-SB3KW-S		1	◇◇◇◇◇◇	
SWT4-8-B3000-SB3KW-S		1	◇◇◇◇◇◇	

Design Adapter			
Part Number	◇◇◇◇◇◇◇◇◇	◇◇◇◇◇◇	◇◇◇◇◇◇◇◇◇◇◇
SWT4-1-5C000-SF0BW-S	◇◇	SC UPC	◇◇
SWT4-1-6C000-SB0KW-S	◇◇	SC APC	◇◇
SWT4-1-6C000-SF0BW-S	◇◇	SC APC	◇◇
SWT4-1-6C44H-SB3KW-S	◇◇	SC APC	◇◇
SWT4-1-6W000-SB0KW-S	◇◇	SC APC	◇◇
SWT4-1-6W000-SB3KW-S	◇◇	SC APC	◇◇

Small Wall Terminal (SWT)



Design Adapter			
Part Number	□□□□□□□□	□□□□□	□□□□□□□□
SWT4-1-6W44H-SB3KW-S	□□	SC APC	□□
SWT4-2-6C000-SB0KW-S	□□	SC APC	□□
SWT4-2-6C000-SB3KW-S	□□	SC APC	□□
SWT4-2-6C000-SF0BW-S	□□	SC APC	□□
SWT4-2-6C000-SF3BW-S	□□		□□
SWT4-2-6C44H-SB3KW-S	□□	SC APC	□□
SWT4-2-6S000-SF0BW-S	□□	SC APC	□□
SWT4-2-6S44H-SB3KW-S	□□	SC APC	□□
SWT4-2-6W000-SB3KW-S	□□	SC APC	□□
SWT4-2-6W000-SF3BW-S	□□		□□
SWT4-2-6W44H-SB3KW-S	□□	SC APC	□□
SWT4-4-04000-SF0BW-S	□□	LC UPC	□□
SWT4-4-5C000-SF0BW-S	□□	SC UPC	□□
SWT4-4-6C000-SB0KW-S	□□	SC APC	□□
SWT4-4-6S44H-SB3KW-S	□□	SC APC	□□
SWT4-4-6W000-SB3KW-S	□□	SC APC	□□
SWT4-4-BS000-SB3KW-S	□□	LC APC	□□
SWT4-8-B3000-SB3KW-S	□□	LC APC	□□

Dimension			
Part Number	□□	□□	□□
SWT4-1-5C000-SF0BW-S	103 mm	75 mm	25 mm
SWT4-1-6C000-SB0KW-S	103 mm	75 mm	25 mm
SWT4-1-6C000-SF0BW-S	103 mm	75 mm	25 mm
SWT4-1-6C44H-SB3KW-S	103 mm	75 mm	25 mm
SWT4-1-6W000-SB0KW-S	103 mm	75 mm	25 mm
SWT4-1-6W000-SB3KW-S	103 mm	75 mm	25 mm
SWT4-1-6W44H-SB3KW-S	103 mm	75 mm	25 mm

Small Wall Terminal (SWT)



Dimension			
Part Number	◇◇	◇◇	◇◇
SWT4-2-6C000-SB0KW-S	103 mm	75 mm	25 mm
SWT4-2-6C000-SB3KW-S	103 mm	75 mm	25 mm
SWT4-2-6C000-SF0BW-S	103 mm	75 mm	25 mm
SWT4-2-6C000-SF3BW-S	103 mm	75 mm	25 mm
SWT4-2-6C44H-SB3KW-S	103 mm	75 mm	25 mm
SWT4-2-6S000-SF0BW-S	103 mm	75 mm	25 mm
SWT4-2-6S44H-SB3KW-S	103 mm	75 mm	25 mm
SWT4-2-6W000-SB3KW-S	103 mm	75 mm	25 mm
SWT4-2-6W000-SF3BW-S	103 mm	75 mm	25 mm
SWT4-2-6W44H-SB3KW-S	103 mm	75 mm	25 mm
SWT4-4-04000-SF0BW-S	103 mm	75 mm	25 mm
SWT4-4-5C000-SF0BW-S	103 mm	75 mm	25 mm
SWT4-4-6C000-SB0KW-S	103 mm	75 mm	25 mm
SWT4-4-6S44H-SB3KW-S	103 mm	75 mm	25 mm
SWT4-4-6W000-SB3KW-S	103 mm	75 mm	25 mm
SWT4-4-BS000-SB3KW-S	103 mm	75 mm	25 mm
SWT4-8-B3000-SB3KW-S	103 mm	75 mm	25 mm

Ordering Information

Part Number	◇◇◇◇◇◇◇◇
SWT4-1-5C000-SF0BW-S	1/1
SWT4-1-6C000-SB0KW-S	1/1
SWT4-1-6C000-SF0BW-S	1/1
SWT4-1-6C44H-SB3KW-S	1/1
SWT4-1-6W000-SB0KW-S	1/1
SWT4-1-6W000-SB3KW-S	1/1
SWT4-1-6W44H-SB3KW-S	1/1

Small Wall Terminal (SWT)



Part Number	◆◆◆◆◆◆◆◆
SWT4-2-6C000-SB0KW-S	1/1
SWT4-2-6C000-SB3KW-S	1/1
SWT4-2-6C000-SF0BW-S	1/1
SWT4-2-6C000-SF3BW-S	1/1
SWT4-2-6C44H-SB3KW-S	1/1
SWT4-2-6S000-SF0BW-S	1/1
SWT4-2-6S44H-SB3KW-S	1/1
SWT4-2-6W000-SB3KW-S	1/1
SWT4-2-6W000-SF3BW-S	1/1
SWT4-2-6W44H-SB3KW-S	1/1
SWT4-4-04000-SF0BW-S	1/1
SWT4-4-5C000-SF0BW-S	1/1
SWT4-4-6C000-SB0KW-S	1/1
SWT4-4-6S44H-SB3KW-S	1/1
SWT4-4-6W000-SB3KW-S	1/1
SWT4-4-BS000-SB3KW-S	1/1
SWT4-8-B3000-SB3KW-S	1/1



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • ◆◆
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/emea/trademarks. Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2026 Corning Optical Communications. All rights reserved.