

# Two-Post Rack

The CORNING logo is displayed in white, uppercase letters on a solid blue rectangular background.

## Features and Benefits

### **Triple U Rail High load capacity**

~ 1000 lbs for 2-Post and ~ 3000 lbs for 4-Post

---

### **EIA 310 Compliant**

Compliant for global use

---

### **48U Rack space**

Compliant with other 7-ft 2-Post Racks with other heights and U-space available

---

### **Available in various colors**

Platinum, Gray, Black, White

---

### **All Steel Construction**

Durable and robust

---

### **Available Accessories such as Jumper Manager, Jumper Manager Doors, Cable Manager and Side Panels**

Scalable to any application at point of installation or future

# Two-Post Rack

The CORNING logo is displayed in white, uppercase letters on a dark blue rectangular background.

## Specifications

### General Specifications

Access Type	front and rear access fixed
Application	Data Center , LAN , Enterprise Networks , DAS (wireless)
Mounting Type	Rack 19-in

### Dimension

Part Number	Height	Width	Depth
PR2ADJAA1NNNNNNN0PFWF	2200 mm	516 mm	579 mm

## Ordering Information

Part Number	Units per Delivery	Weight	Package Contents
PR2ADJAA1NNNNNNN0PFWF	1/1	33 kg	19- Inch Two-Post Rack 2.2m, Installation Guide



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States  
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • [www.corning.com/opcomm](http://www.corning.com/opcomm)

A complete listing of the trademarks of Corning Optical Communications is available at [www.corning.com/opcomm/emea/trademarks](http://www.corning.com/opcomm/emea/trademarks). Corning Optical Communications is ISO 9001 and ISO 14001 certified. © 2022 Corning Optical Communications. All rights reserved.