

Two-Post Rack

The CORNING logo is displayed in white, uppercase letters on a solid blue rectangular background.

Features and Benefits

Triple U Rail High load capacity

~ 1000 lbs for 2-Post and ~ 3000 lbs for 4-Post

EIA 310 Compliant

Compliant for global use

48U Rack space

Compliant with other 7-ft 2-Post Racks with other heights and U-space available

Available in various colors

Platinum, Gray, Black, White

All Steel Construction

Durable and robust

Available Accessories such as Jumper Manager, Jumper Manager Doors, Cable Manager and Side Panels

Scalable to any application at point of installation or future

Two-Post Rack



Specifications

General Specifications	
Access Type	front and rear access fixed
Application	Data Center , LAN , Enterprise Networks , DAS (wireless)
Mounting Type	Rack 19-in



Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC • 28216 • United States
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2024 Corning Optical Communications. All rights reserved.