

Corning SpiderCloud SCRN-220 Radio Node for Enterprise Radio Access Network (E-RAN)



Features and Benefits

Supported service	LTE small cell with support for Rel 13 IOT features
Supported bands/channels	Software-configurable LTE radio bands
Capacity	128 active users
Performance	150/50 Mbps peak DL/UL LTE throughput (with 20 MHz licensed channel)
SON	Built-in self-organizing networks (SON) features for ease of deployment for seamless mobility with macro network
Fronthaul network	Deployable over existing Ethernet switching infrastructure (VLAN)
Power source	Power-over-Ethernet (PoE+)
Installation	Wall and ceiling mountable
Authentication	Certificate-based authentication with SpiderCloud services node

High-performance LTE small cell for scalable indoor and venue deployments

The SCRN-220 is an integrated LTE small cell with support for Rel13 IOT devices.

The SpiderCloud® scalable small-cell system, called an enterprise radio access network (E-RAN), hides the complexity of radio management and mobility and provides operators with a single touchpoint to aggregate and manage a large network of LTE small cells.



SCRN-220 | Figure 1


Corning SpiderCloud SCRN-220 Radio Node for Enterprise Radio Access Network (E-RAN)



Functional Overview

Radio Capabilities	Each SCRN-220 supports 2 x 2 MIMO operation on configurable LTE bands, enabling higher-user capacity and average data rates per radio node coverage footprint. Each LTE carrier supports 128 active LTE users, of which 64 can be VoLTE users. When used with 20 MHz channel bandwidth, an LTE carrier supports a peak downlink rate of 150 Mbps and a peak uplink rate of 50 Mbps.
Self-Organizing Networks	The radio node implements SON capability by listening to other radio nodes within the E-RAN and neighboring LTE macro cells in multiple frequency bands, and performing continuous self-optimization to provide high-quality radio coverage and mobility.
Easy to Install	SpiderCloud® radio nodes can be installed on walls or ceilings. Both network connectivity and power are provided over Ethernet. The radio node has no fans and is completely convection cooled. Antennas are built in for both LTE bands, with an orderable option for QMA connectors for use with external antennas.
Secure	SCRN-220 utilizes on-chip trusted platform module (TPM) functions to implement secure boot, and establish certificate-based IPsec tunnel to SpiderCloud services node for all LTE traffic. There is no management or console port on the radio node, and the radio node can be physically locked to prevent theft.

Corning SpiderCloud SCRN-220 Radio Node for Enterprise Radio Access Network (E-RAN)



Building Diagram | Figure 2

Corning SpiderCloud SCRN-220 Radio Node for Enterprise Radio Access Network (E-RAN)



System Specifications

Security	Secure boot and secure key storage using trusted platform module (TPM) functions IPsec tunneling to services node X.509 certificate-based authentication
Timing and Synchronization	IEEE 1588v2-based (PTP) synchronization to services node
Ciphering	SNOW 3G and AES air interface encryption

Corning SpiderCloud SCRN-220 Radio Node for Enterprise Radio Access Network (E-RAN)



Radio Specifications

Performance

- Peak rates: 150/50 Mbps DL/UL (with 20 MHz)
- 128 active users, of which 64 can be VoLTE
- Support for Rel 13 IOT features

Licensed Radio

- Multiple band class options (see product SKUs)
- Channel sizes: 5, 10, 15, 20 MHz
- 2 x 2 MIMO
- Maximum transmit power: 2 x 250 mW (27 dBm)

Mobility

- Inter radio node handover anchored at the services node
- Inter-frequency S1 handover to/from macro
- Intra-frequency S1 handover to/from macro

RF Management

- LTE network listen
- Inter- and intra-frequency neighbor cell detection
- Auto assignment of physical cell identities (PCI)
- Automatic neighbor relation (ANR) management

Radio Specifications (cont.)

QoS Features

- Support for all LTE QCI
- Guaranteed bit rate (GBR)
- Maximum bit rate (MBR)
- Aggregate maximum bit rate (AMBR)

Voice Services

- VoLTE
- Eight data radio bearers (DRB) per UE

Corning SpiderCloud SCRN-220 Radio Node for Enterprise Radio Access Network (E-RAN)



Physical Specifications (cont.)

Enterprise Installation Wall and ceiling mountable
 Mounting hardware included
 Padlock option
 Power-over-Ethernet: 802.3at
 Power consumption: 20 W

LED Indication 1 x tri-color LED (RGB)

 Status indications: boot, normal,
 disabled, fault, emergency call,
 radio node tracking

Antenna Options Two internal Tx/Rx antennas
 (peak gain 5 dBi)

 Option for QMA antenna connectors
 for use with external antennas.
 Orderable as separate SKU.

Physical and
Environmental Dimensions: 183 x 183 x 36 mm
 (7.2 x 7.2 x 1.4 in)

 Weight: 1.23 kg (2.7 lbs)

 1 x 1000 Mbps Ethernet (RJ45)

 Operating temperature: 0 to 40°C

 Storage temperature: 0 to 85°C

 Operating humidity: 0 to 90%
 noncondensing

 Storage humidity: 0 to 90%
 noncondensing

 Ingress protection rating: IP30

Regulatory Compliance and Certification

Certifications Safety EN 60950, CB certification
 (IEC 60950, UL 60950-1)

 FCC Part 15, Class A

 FCC Part 24 and 27

 General CE and NRTL marking

 MPE: FCC 47 CFR 1.1307(b)



Corning SpiderCloud SCRN-220 Radio Node for Enterprise Radio Access Network (E-RAN)



Ordering Information

Part Number	Description
SCRN-220-020412	Configurable single-mode LTE cell SW configurable licensed band with support for Band 4 (66), Band 2 (25), or Band 12 Monitors LTE 700/1900/2100 MHz
SCRN-220-020412-EQ	Same as SCRN-220-020412 with QMA antenna connectors for external antennas
SCRN-220-020413	Configurable single-mode LTE Cell SW configurable licensed band with support for Band 4 (66), Band 2 (25), or Band 13 Monitors LTE 700/1900/2100 MHz
SCRN-220-020413-EQ	Same as SCRN-220-020413 with QMA antenna connectors for external antennas

Corning SpiderCloud SCRN-220 Radio Node for Enterprise Radio Access Network (E-RAN)



Notes:

**Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA
800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm**

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified.

© 2018, 2019 Corning Optical Communications. All rights reserved.