




CORNING

Central Office Decision Matrix

CORNING



	EDGE8® SOLUTIONS	CENTRIX™ SYSTEM	Enhanced Management Frame (EMF)	ECLIPSE® HARDWARE
	Higher Density			Lower Density
New Installation	Applicable	Ideal	Applicable	Ideal
Frame Configuration	19-in or 23-in	High-density/19-in/23-in/ front and rear cable access configurations	High-density	19-in or 23-in
Capacity in 7-ft Frame	5,760 LC	2,880 SC/4,320 LC (3,840 WITH PON splitters)	1,728 per side (3,456 total LC)	1,440 (864 with PON splitters)
Wall-Mountable Option			√	√
Cable Type	LSZH™, plenum, I/O, distribution, FREEDM® ribbon, and LT	ALTOS® dielectric gel-free LT, ribbon riser, SST-Ribbon™, FREEDM ribbon riser, FREEDM IN/OUT LT, MiniXtend® standard LT, ALTOS riser LT cable	ALTOS dielectric gel-free LT, ribbon riser, SST-Ribbon, FREEDM ribbon riser, FREEDM IN/ OUT LT, ALTOS riser LT cable	ALTOS dielectric gel-free LT, ribbon riser, SST-Ribbon, FREEDM ribbon riser, FREEDM IN/OUT LT, ALTOS riser LT cable
Connector Type	LC, MTP®	SC, LC, MTP	SC, LC, MTP	SC, FC, LC
Jumper Size	1.6 mm	2.0 mm SC / 1.6 mm LC	2.0 mm	2.0 mm
Devices, CWDM, Triplexers, and Quadplexers		√	√	√
Accommodate Splitters		√	√	√
Port Tapping	√	√		
On-Frame Splicing	√	√	√	√
Removable Housing Cover	1U and 2U		√	
Quick Facts	<ul style="list-style-type: none"> Base-8 fiber applications Tip-to-tip solution for data centers and storage area networks (SANs) Ideal for structured cabling in a data center Housings, modules, panels, trunks, harnesses, and jumpers 	<ul style="list-style-type: none"> GR-449 Issue 3 compliant Scalable in features and function Industry-leading cable and jumper management Enclosed 4U housing option available Versatile cassette/modules including staggered LC cassettes 	<ul style="list-style-type: none"> Integrated fiber routing guides Individual 12 F modules that extend/retract independently Single-jumper length Up to 24 F modules 	<ul style="list-style-type: none"> Integrated fiber management Front-to-back jumper access Splitter compatible with OptiTect® Gen III and LS series



Optical Splice Enclosure
<p>OSE-UD0-00-3</p> <p>5,184 single-fiber/6,912 mass fusion ribbon splices</p>
<p>OSE-HD0-00-1</p> <p>1,440 single-fiber/360 mass fusion ribbon splices (4,320 fibers)</p>
<p>OSE-HD2-00-1</p> <p>1,008 single-fiber splice</p>
<p>OSE-LD0-00-1</p> <p>576 single-fiber/144 mass fusion ribbon splices (1,728 fibers)</p>
<ul style="list-style-type: none"> Wall, 23-in rack and T-slot mountable Seven watertight compression fittings Heat-shrink, RTV, and mass-fusion splice trays

Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA
 800-743-2675 • FAX: 828-325-5060 • International : +1-828-901-5000 • www.corning.com/opcomm

Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. ©2019 Corning Optical Communications. All rights reserved. CRR-1057-AEN / March 2019