Know Your FlexNAP[™] System

CORNING

Do you know the benefits of the Corning FlexNAP[™] system? Our FlexNAP system provides the most cost-effective method of deploying optical fiber in distribution networks at speeds significantly faster than traditional field installations. The increased speed of network deployment, along with the reliability of factory testing, offers significant value to you.

Up to 5x Faster

plus 5x reduction in civil traffic/customer disruptions, when compared to traditional field installations.




Reduced Supply Chain/Installation Complexity

Fewer components to manage in the field.



Slimline Overmolds



Reduces product space requirements.

Increased Labor Efficiency

Faster subscriber turn-up using same crew.





80% fewer field splice locations and up to 70% fewer splices total, when compared to traditional field deployments.

Widespread Adoption

of homes using OptiTip[®] technology solutions.



Proven Reliability

with 99% of the buried network remaining operational during Hurricane Harvey (2017).



Factory Quality 100% _{factory-tested components.}



Simple Repairs

Cable repair with standard procedures and practices.

Full Preconnectorized

Full Splice

Cable cuts managed similarly to bulk cable deployments.



Plan your deployment

Let's get ready to start your FlexNAP[™] design.

1 Pick your cable type

(Aerial is typically a 5 ft tether; Buried is typically a 15 ft tether)

- Aerial RPX[®] or loose tube
- Buried Toneable RPX or armored loose tube
- Duct Toneable RPX or loose tube

2 Pick your tether locations

- How many homes do you want to serve per location? 2, 4, 6, 8, or 12 homes per tether loose tube 4, 8, or 12 homes per tether RPX
- Do you need one tether or more per location? Once you know your tethers, you can move to your terminal selection

3 Make your terminal selection

- Aerial Evolv[™] terminal or MDU terminal products
- Buried or duct Evolv terminal or MDU

4 Drop Style Selection

Is your drop terminating inside or outside the house?

Outside ONT


ROC[™] drop with home side typically SC APC or pigtail (assume connectorization or splice in field)

Inside ONT

ROC drop to transition housing or indoor/outdoor ROC drop to indoor ONT

5 Next Steps

Give us a call for product pricing, design support, or cable configuration. Contact 828-901-5000 today!







Plan your deployment

Let's get ready to start your FlexNAP[™] design.

1 Pick your cable type

(Aerial is typically a 5 ft tether; Buried is typically a 15 ft tether)

- Aerial SST-Drop[™] or loose tube
- Buried Toneable SST-Drop or armored loose tube
- Duct Toneable SST-Drop or loose tube

2 Pick your tether locations

- How many homes do you want to serve per location? 1 or 2 fibers per tether
- Do you need one tether or more per location? Once you know your tethers, you can move to your terminal selection

3 Make your terminal selection

- Aerial Evolv[™] splitter terminal or MDU terminal products
- Buried or duct Evolv splitter terminal, or LPT terminal with splitter

4 Drop Style Selection

Is your drop terminating inside or outside the house?

Outside ONT


ROC[™] drop with home side typically SC APC or pigtail (assume connectorization or splice in field)


Inside ONT

ROC drop to transition housing or indoor/outdoor ROC drop to indoor ONT

5 Next Steps

Give us a call for product pricing, design support, or cable configuration. Contact 828-901-5000 today!





Loose Tube Cable



LPT Terminal with Splitter

ROC Drop Pigtail



- 21

Connect your subscribers

You have subscribers. Now what?



1 Install Cable





2 Install Terminals







	Aerial Pole or Buried		Façade/F	
	REALERED	Totototte		The second se
	Evolv [∞] Terminal	Evolv Splitter Terminal	MDU Terminal	Low-Profile Terr
	Centralized	Distributed	Centralized, home run	Centralized, home run
y	2, 4, 6, 8, 12 ports	4, 8 ports	6, 12, 24, 36, 48 fibers	4, 6, 8, 12 fibers

OptiTap single-fiber hardened connector (female)

The multiport stubless splitter terminal offers split ratios of 1x4 or 1x8

input port for fast terminal connection to OptiTap enabled tethers.

in the same trusted, sealed terminal. A blue connector cap identifies the

FlexNAP Single-Fiber System

Architecture

Drop Capacity

Connector Type

FlexNAP[™] System

Compatibility

Quick Facts

OptiTip[®] multifiber hardened connector

The standard multiport terminated with an OptiTip stub is our most pop-

ular terminal choice in the OSP for centralized split architectures. Its fully

in three body sizes to accommodate 2/4, 6/8 or 12-fiber options.

sealed terminal body is suitable for all environments (rated IP-68). Available

FlexNAP Standard System

OptiTip[®] multifiber hardened connector

The MDU terminal equipped with OptiTip stubs

or multidwelling unit buildings. With 24-, 36-, or

conceal excess drop cable length.

48-fiber capacity, these façade-mount terminals are

ideal for including in standard SFU deployments in

mixed-use neighborhoods and towns. The MDU has

an additional slack-management housing and skirt to

support medium-density multitenant business parks

FlexNAP Standard System

/Pole

FlexNAP Standard System



"Without a doubt, one of the key things that made this project successful from the start was more than just Corning's industry-leading products; it was their engineering expertise that helped me figure out how to be successful from planning to implementation and now to growth."

-Mike Bosch, CEO of RG Fiber

"From a project management point of view, working with Centrix[™] and FlexNAP[™] systems is a dream for scheduling and coordination. We are no longer dependent on splicing contractors once the fiber goes up."

-Brenden Griswold, Operations Coordinator, OTTC

"Since the subscriber connection is such a simple process, I can easily employ local talent to build out the final piece of the network. I don't need to find someone outside the community with years of fusion splicing experience to guarantee fast installation and the highest transmission speeds for my customers."

-Greg Dynek, CEO of Bluestem Fiber

We are here. We understand. We can help.

Ready to configure? Whether you are maintaining your infrastructure to stay ahead of bandwidth demand or building your network from the ground up, you have scores of decisions to make – and every one of them can impact your bottom line. Before exploring specific connectivity products, connect with us for value that extends well beyond our portfolio.

We'd be happy to discuss the details of your broadband vision and can provide you with a cost analysis that compares the speed and cost of deployment for a full-splice, semi-precon, and full-precon deployment in your community.

Learn more at www.corning.com/community-broadband/next-steps

To learn more about the FlexNap design tool visit:

www.corning.com/flexnap

CORNING

Corning Optical Communications LLC • 4200 Corning Place • Charlotte, NC 28216 USA 800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2019, 2023 Corning Optical Communications. All rights reserved. CRR-1014-AEN / February 2023