




# With Corning® CleanAdvantage™ technology we take care of the cleaning process for you!

As a leader in optical fiber and connectivity, Corning understands the value of clean connectors to ensure optical performance. So much so that we have developed a new factory cleaning and sealing process, Corning® CleanAdvantage™ technology, to ensure a pristine end face upon first use for all our EDGE™ and EDGE8® solutions. Thus, saving you as the installer time and money during the initial installation. So go ahead and uncap that CleanAdvantage connector so that you can connect with confidence.

-  **Save up to 17% install time**  
No need for cleaning or visual inspection before the first install.
-  **Save up to 95% on consumables**  
No cleaning pens, cassettes, and wipes necessary.
-  **Minimizes debris transfer**  
Reduces the risk of debris transfer on the end face, minimizes signal degradation.
-  **Standardized offering**  
High density paired with high performance at no extra cost.



Learn more at [corning.com/cleanadvantage](http://corning.com/cleanadvantage)