## CORNING

# Everon<sup>®</sup> CIP-01-56V Corning Intelligent Power (CIP)



The Everon<sup>®</sup> CIP-01-56V power supply unit provides a National Electrical Code<sup>®</sup> (NEC<sup>®</sup>) Class-2 LPS 56V output that allows various output power characteristics achieved via connectivity to an external (and thus, modular) aggregator and step-down converter units.

- Step-down converters allow voltage reduction from 56 V to 24 V, supporting up to 95 W loads.
- **Aggregators** allow power aggregation of two or eight CIP-01-56V units to provide up to 720 W of power.
  - Please see **step-down converter and aggregator data sheets** for more information.

Corning's Everon single channel PSU provides the following main enhancements:

Status LEDs

Features	Benefits	
Application	SD-LAN, Software Defined Access Nodes (SDANs), Distributed Antenna Systems/Small Cell Radio Nodes,and other Low Voltage Network devices that accept 56 VDC power.	WLAN APs, Security Cameras, Access Control, Building Automation, and other Low Voltage powered devices.
Common Power Source Features	AC input range: 100 VAC to 240 VAC/2A max • Passive cooling • Output port option: Single-port model with paralleling option • Output power of up to 95 W	<ul> <li>High efficiency up to 92%</li> <li>Built-in monitoring and control:</li> <li>Overtemperature, overload</li> <li>Protections: short circuit, overload, overvoltage, and overtemperature</li> <li>Outputs protection auto-recovery</li> </ul>
Mounting Options	Wall/Surface mount brackets (included) Optional - Din rail mounting bracket (1LAN-FMC-DINBRACKET) Optional - Low Profile bracket for mounting flat inside of enclosure (1LAN-D600-FMC-KIT)	

#### System Architecture

Important safety-related notes to read prior to installation

The system must be installed and used in accordance with all applicable local, state, and national electric codes.

Two CIP-01-56V units can be paralleled by using a Cat.5/6 RJ45 jumper from the output sync port of first CIP-01 into the input sync port of the second CIP-01.

Paralleled CIPs will be load balanced and can then be used to feed a 2x1 AGG and/or 8x1 AGG.

Connect the Sync output of the first CIP to the Sync input of the next CIP, and so on and so forth for each unit to accommodate aggregation.

### Specifications

Environmental Specifications				
Working temperature	-20°C to +60°C			
Working humidity	0% to 90% RH non-condensing			
Storage temperature	-20°C to +85°C			
Storage humidity	10% to 95% RH			
Vibration	10 Hz to 500 Hz, 2G 10 min/cycle, 40 min each along X, Y, Z axes			

Physical Specifications				
Dimensions	127 x 105 x 50 mm			
Weight	0.63 kg			

Power Specifications				
Input power source	Universal AC 100-240 VAC			
Max. power consumption	1 Port: Max 130 W			
Max. input current	1.5A with 100 VAC			
Output port power	56 VDC Maximum Output Power 95 W ± 5%			

Standards and Certifications				
EMC	FCC CFR 47 Part 15 Subpart B, EN 55035:2017, EN 55032:2015, CISPR 32, AS/NZS CISPR 32:2012, EN 61000-3-2:2014, EN 61000-3-3:2013, EN 61000-4-8:2010			
Safety compliance	UL/EN/IEC 62368-1 Edition 2 as a LPS (Limited Power Source)			
Regulatory Compliance	CE / UKCA			

#### **Ordering Information**

Description	Part Number
Class-2 power supply, 56 VDC, 1 channel, mini form factor	CIP-01-56V
Mounting kit for 1LAN-FMC-10G into 1LAN-D600-ENC-3 outdoor enclosure	1LAN-D600-FMC-KIT
Din Rail Accessory Bracket for FMC	1LAN-FMC-DINBRACKET
EN 50022 – 35 × 7.5 (1 meter) (DIN RAIL)	1LAN-SDAN-DIN1160
19-in rack mount shelf with 2U blank plates	CIP-19SHELF-2U
L Bracket w/ DIN rail for CIP shelf	CIP-19SHELF-DIN
Two Class-2 inputs per aggregator (supports 24 VDC to 56 VDC Class-2 inputs x 2) cable-side Dinkle connectors are attached to the unit	CIP-AGG-2 2-Port Aggregator
Eight Class-2 inputs per aggregator (supports 24 VDC to 56 VDC Class-2 inputs x 8) cable-side Dinkle connectors are attached to the unit	CIP-AGG-8 8-Port Aggregator
Class-2 56 VDC to 24 VDC step-down converter (up to 90 W input distributed over two 24 V ouputs) Multiple CIP-VC-56T24 converter outputs that are powered from 56 VDC Corning <sup>®</sup> Everon <sup>®</sup> PSU ports may be aggrevated with the 2- or 8-port aggregator to feed big loads	CIP-VC-56T24 Step-Down Converter

## CORNING

Corning Optical Communications GmbH & Co. KG - Leipziger Strasse 121 - 10117 Berlin, GERMANY

+00 800 2676 4641 • FAX: +49 30 5303 2335 • www.corning.com/opcomm/emea Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2024 Corning Optical Communications. All rights reserved. LAN-3180-A4-BEN / September 2024