
# CORNING





## Corning<sup>®</sup> Magnesium Fluoride (MgF<sub>2</sub>)

#### Flouride Crystal Materials

Corning is a premier provider of fluoride crystal materials, one with the expertise and resources required to provide complete end-to-end optical solutions. Our crystal growth operation regularly produces Magnesium Fluoride crystals of exceptional quality for use at a variety of wavelengths and in a multitude of applications. In addition to growing crystal materials, Corning also offers designing, fabrication, polishing, and coating capabilities. With the ability to do it all under one roof, let Corning be the supplier of choice for your most complex optical requirements.

Magnesium Fluoride is a durable crystal with low absorption, suitable for high-powered laser, space, and other UV applications. MgF, is also naturally birefringent, making it an ideal material for use where this property can be exploited, such as retardation plates and polarizing elements, particularly in the wavelength range from 0.13-0.30 μm. Single crystal ingots are grown exclusively in the USA from highly purified materials using Corning's proprietary process, ensuring consistent supply. A full range of geometries and finishes, from ingots and blanks to complex multi-faceted, highly polished parts are available. Standard (001) orientation as well as specifically oriented parts and materials are offered. A variety of finishes and coatings can be customized and combined to meet individual customer specifications.

## Physical and Chemical Properties

#### **General Properties**

7780-40-6	
62.302 g/mol	
Tetragonal, TiO2 Rutile type, space group P4 <sub>2</sub> /mnm, ao = 4.623Å, C <sub>o</sub> = 3.52Å	
3.177 g/cm³ at 20 °C	
1255 °C	
2260 °C	

#### Mechanical and Electrical Properties

Bulk Modulus	101.3 GPa		
Shear Modulus	54.7 GPa		
Young Modulus	139.0 GPa		
Poisson's Ratio	0.271		
Elastic Constants Elastic Stiffness (GPa)	$C_{11} = 123.7$ $C_{12} = 73.2$ $C_{33} = 177.0$ $C_{13} = 53.6$ $C_{44} = 55.2$ $C_{66} = 95.1$		
Dielectric Constant	4.87 along C axis, 5.45 perpendicular between 95KHz and 42MHz		
Hardness	415 Knoop		

Issued May 2018 1

#### Thermal Properties

#### **Heat Capacity**

T[K]	Cp [J/g · K)]
80.00	0.238
95.00	0.319
114.00	0.428
135.00	0.538
155.00	0.627
176.00	0.706
196.00	0.771
216.00	0.830
236.00	0.877
256.00	0.922
276.00	0.955
	·

#### Thermal Conductivity

T[°C]	[W/(m·K)]
18	11.6

#### Linear Thermal Expansion Coefficient


T [°C]	T [K]	Coefficient [x10 <sup>-6</sup> /K]	
		Perp c axis	Parallel c Axis
-180	93	0.72	2.90
-160	113	1.63	4.45
-140	133	2.65	5.95
-120	153	3.64	7.39
-100	173	4.58	8.86
-80	193	5.45	9.82
-60	213	6.23	10.86
-40	233	6.93	11.74
-20	253	7.52	12.47
0	273	8.04	13.07
20	293	8.48	13.70
40	313	8.88	14.09
60	333	9.25	14.54
80	353	9.60	14.94
100	373	9.93	15.32
120	393	10.22	15.67
140	413	10.49	16.00
160	433	10.71	16.33
180	453	10.91	16.67
200	473	11.10	17.00

#### **Optical Properties**

Transmission Range	Useful range of 0.11 μm to ~7.50 μm, depending on thickness	
Energy Gap	11eV	
Restrahl Frequency	17.5, 20.8, 24.7, 34.5, and 37.0 μm	
Reciprocal Dispersive Power	100	

#### Sample Transmission and Index of Refraction

(5mm thickness, uncorrected for surface effects)



# Available Grade and Additional Information

Corning® Magnesium Fluoride material is classified as Excimer ArF grade. For the most demanding high-fluence applications, Corning® Calcium Fluoride 193 nm Laser Durability Gradeis also available.

Corning's crystal experts work actively with every prospective customer to determine the most appropriate and cost-effective solution for each application. Depending on the application of interest, some or all of the following attributes may be considered in the selection process:

>99.0% @ 193.3nm	
Naturally birefringent	
ISO 10110 - 1/1 x 0.02	
To 10/5 available	
To 2 Å available	
1.7", 2.4", 3.5" and 5" (typical), others upon request	
Typically at least one face parallel to (001), which is perpendicular to the optical "C" axis [001], others upon request	
Saw cut, fine ground, polished, super-polished, enhanced super-polished	
Anti-reflective, highly reflective, partially reflective, low absorption, custom solutions upon request	

Issued May 2018 2

Depending on customer requirements, Corning can provide solutions ranging from crystal blanks to complete turnkey optical packages. We can precisely manufacture a wide variety of laser optic components including windows, prisms, and mirrors, as well as plano convex, plano concave, and hemispherical optics. With world-class coating engineering expertise, we can customize final optical performance to enhance transmission, reflectivity, and/or laser durability to your specification in order to provide a comprehensive optical path solution.

## **CORNING**

For more information about fluoride crystals please contact us at:

Email: \_TropelCustomerService@corning.com www.corning.com/advanced-optics

© 2018 Corning Incorporated. All Rights Reserved.

#### Sales Offices:

Corning Tropel Corporation 60 O'Connor Road Fairport, New York 14450, United States Phone: (585) 388-3500; Fax: (585) 377-1966

Corning GmbH - Corning International Abraham-Lincoln Strasse 30 D-65189 Wiesbaden, Germany Phone: 49-611-7366-100; Fax: 49-611-7366-143

Corning International K.K. 11-44, Akasaka 1-Chrome Minato-ku, Japan

Phone: 81-3-5562-2260; Fax: 81-3-3224-1405

Corning Singapore Holdings Private Limited 1, Kim Seng Promenade Great World City #9-11/12 West Tower 237994, Singapore Phone: 65-6572-9740; Fax: 65-6735-2913

Corning Display Technologies Taiwan Co., Ltd. 8F., No. 8, Sec. 3, Minsheng E. Rd. Zhongshan District, Taipei City, Taiwan 10480, China Phone: 886-2-2716-0338

Corning China (Shanghai) Regional Headquarters No. 358 (Gate #4), Lu Qiao Road Jinqiao Export Processing Zone Pudong Shanghai 201206, China Phone: 86-21-5467-4666; Fax: 86-21-5407-5899

ed May 2018 3