# Corning® RC SMF Specialty Optical Fibers

## CORNING



Low loss fused components for EDFA and small bend radius applications

Manufactured with Corning's patented Outside Vapor Deposition (OVD) process, and based on decades of experience in specialty fiber development, Corning® RC SMF Specialty Fiber sets the industry standard for consistent geometric properties, high mechanical reliability, and efficient splicing.

#### **Applications:**

- Low-loss miniature fused devices for C-band and L-band
- Ultra-compact components requiring small bend radii
- · Pigtails in bend insensitive applications
- Sensors

#### **Features:**

- Outstanding consistency and uniformity using Corning's patented
   Outside Vapor Deposition (OVD) process
- Dual acrylate coating system provides excellent protection from microend-induced attenuation and superior mechanical robustness
- Ultra-tight specifications
- · World-class reliability support for handling and deployment
- Technical support for splicing to 125 μm products
- Ultra-low splice loss to SMF-28e+®
- 80 μm diameter for miniature packaging
- Low bending loss
- Excellent geometry control

#### **Key Optical Specifications**

Operating Wavelength (nm) > 1300			
Fiber Cutoff Wavelength (nm)	≤ 1290		
Maximum Attenuation (dB/km)	0.7 @ 1310 nm 0.5 @ 1550 nm		
Mode-field Diameter (μm)	9.2 ± 0.3 @ 1310 nm 10.4 ± 0.8 @ 1550 nm		

### Key Geometric, Mechanical, and Environmental Specifications

Cladding Outside Diameter (μm)	80 ± 1		
Coating Outside Diameter (µm)	Diameter ( $\mu$ m) 165 ± 10		
Core-to-Cladding Concentricity (μm)	≤ 0.5		
Standard Lengths	500 m, 1 km, 2 km, 5 km, 10 km		
Proof Test (kpsi)	100 or 200		
Operating Temperature (°C)	-60 to +85		

#### **Performance Characterizations\***

Nominal Delta (%)	0.36
Numerical Aperture	0.12
Refractive Index Value – Core	1.458 @ 850 nm
Core Diameter (µm)	8.2
Dispersion (ps/nm/km)	-0.5 @ 1310 nm 16.2 @ 1550 nm

<sup>\*</sup>Values in this table are nomial or calculated values

### **Typical Splice**

	SMF-28e+®	RC HI 1060	RC PANDA PM 1550	RC HI 1060 FLEX	RC HI 980
Wavelength (nm)	1550	1550	1550	1550	980
RC SMF Fiber (dB)	0.05	0.08	0.09	0.12	0.11

For more information about Corning's leadership in Specialty Fiber technology, visit our website at <a href="www.corning.com/specialtyfiber">www.corning.com/specialtyfiber</a>
To obtain additional technical information, an engineering sample or to place an order for this product, please contact us at:

Corning Incorporated

Tel: +1-607-974-9974 Fax: +1-607-974-4122 © 2018 Corning Incorporated



E-mail: specialtyfiber@corning.com

M0500015 Issued: June 2018 Supersedes: April 2016