Single Channel DWDM (200 GHz)



Features and Benefits

High Isolation	
Low Insertion Loss	
Bi-directional	
Epoxy Free in Optical Path	
Completely Passive	

Standards

RoHS Free of hazardous substances according to RoHS2011/65/EU

Design and Test Criteria Product is qualified to Telcordia GR-1209-CORE and

GR-1221-CORE

Corning offers high performance Single Channel Dense WDM for ITU channel spacing applications. The thin film filter DWDM Series of products utilize proprietary technology to deliver exceptional field performance. Single channel DWDMs are available in standard ITU wavelengths from 1528 to 1565 nm. Custom wavelengths and channel configurations are available upon request.



Single Channel DWDM (200 GHz)



Specifications

Parameters	Minimum	Typical	Maximum
Passband Width	$\lambda c \pm 0.25 \text{nm}$		
Pass Channel Insertion Loss		0.8 dB	1.2 dB
Reflection Channel Loss		0.3 dB	0.5 dB
Adjacent Channel Isolation	25 dB	30 dB	
Non-Adjacent Channel Isolation	40 dB	45 dB	
Isolation of Pass Channel @ Reflection Port	12 dB	15 dB	
Optical Return Loss	45 dB	50 dB	
Directivity	50 dB		
PDL			0.1 dB
PMD			0.1 ps
Maximum Optical Power		300 mW	
Operating Temperature Range		-5°C to +65°C	
Storage Temperature Range		-40°C to +85°C	
Tensile Load (900 µm Buffered)		5N Maximum	


Shipping Package		
Packaging Dimensions	Fiber Type	Pigtail Length
<52.5 mm x 4.6 Φmm (Including boots)	Fiber Type: Corning® SMF-28e® or compatible	1 m (Standard)

Single Channel DWDM (200 GHz)



Ordering Information

Single Channel DWDM (200 GHz)



- 1 Select Channel Spacing
 - 1: 200 GHz
 - Z: Others
- 2 Select ITU Grid
 - 2: Standard
 - 5: 50 GHz Shift (less in frequency) from ITU grid
- **Select Wavelength Channel** 00: Non-ITU Specifications
 - NN: ITU Channel, for example, 193.0 THz, NN=30
- **Select Package Type**
 - 0:250 μm Tube 1: 900 µm Tube

 - 2: 250 µm Case
 - 3: 900 µm Case
 - 4: LGX® orRack Mount
 - 5: 3 mm Case
 - 6: 2 mm Case
 - Z: Others

Select Connector*

- A: None
- L: LC/PC
- P: FC/PC
- Q: FC/APC
- S: SC/PC
- T: SC/APC
- U: MU/PC
- Z: Others

Select Customization

000: Standard

Running number used for special types or custom made

Note:

These part numbers are specific to Corning Optical Communications OEM Solutions Business Unit. Please contact OEM sales at +1-408-736-6900 or oemsales@corning.com and visit www.corning.com/opcomm/oem for sales support.



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA 800-743-2675 • FAX: 828-325-5060 • International: +1-408-736-6900 • www.corning.com/opcomm/oem • Email: oemsales@corning.com Corning Optical Communications reserves the right to improve, enhance, and modify the features and specifications of Corning Optical Communications products without prior notification. A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks. All other trademarks are the properties of their respective owners. Corning Optical Communications is ISO 9001 certified. © 2016 Corning Optical Communications. All rights reserved.



^{*} Specifications do not include connector loss.