

Exceptional Dimensional Stability and Surface Quality in Thin, Large-Size Sheets

Corning[®] EAGLE XG[®] Glass is considered the most widely used and trusted glass by the world's leading panel makers, and was the first glass composition to include no heavy metals. Available in the widest variety of form factors, EAGLE XG[®] Glass can be made as thin as 0.25 mm up to Gen 5.5, 0.3 mm up to Gen 6, 0.4 mm up to Gen 8.5, and 0.5 mm up to Gen 10.5 to enable thinner, lighter, and curved display panels.

Product & Material Information

Corning[®] EAGLE XG[®] Glass is produced to the following type specifications:

Material Information		Electrica	al				
Glass Type	Alkaline Earth Boro-Aluminosilicate			Dieleo	tric Constant		
Forms Available	Fusion Drawn Sheet		10				200 Hz
Principle Uses	Substrates for active-matrix flat panel displays		9.5 - 9 -				
Mechanical Properties	Density (20°C)	2.38 g/cc ³	₽ 8.5			_/	 1 KHz
	Young's Modulus	73.6 GPa	ectri 8 –				
	Shear Modulus	30.1 GPa	<u> </u>				-
	Poisson's Ratio	0.23	Dielectric Constant 6.5				10 KHz
Thermal Expansion	Coefficient of Thermal Expansion (0 - 300°C)	31.7x10 ⁻⁷ / °C	6 5.5 5				100 KHz
	Room Temperature to Setting Point	35.5x10 ⁻⁷ / °C (25-675°C)	0	Dielec	300 400 mperature °C tric Constant: 5.27 °C/68 °F –1KHz)	500 6	00
	Working Point (104 poises)	1293°C		Dissi	pation Factor		
Viscosity	Softening Point (10 ^{7.6} poises)	971°C	10 		(Loss rungent)		200 Hz
	Annealing Point (10 ¹³ poises)	722°C	sipatio				1 KHz
	Strain Point (10 ^{14.5} poises)	669°C	n Factor 0.1		-H	/	10 KHz 100 KHz
Electrical Properties	Log ¹⁰ Volume Resistivity	12.9 ohm- cm at 250°C	0.01		11//		-
		<i>8.8 ohm- cm</i> at 500°C	Dissipation Factor (Loss Tangent)				-
Optical Properties	Birefringence Constant	331 (nm/cm) /(kg/mm²)	0.001				
			0	200 Te	400 mperature °C	6	00

Chemical Durability

Chemical durability is measured via weight loss per surface area after immersion. Values are highly dependent upon actual testing conditions. Unless other-wise noted, concentrations refer to weight percent

Reagents	Time	Temp	Weight Loss (mg/cm ²⁾
HCI - 5%	24 hrs	95°C	0.79
HNO3 - 1M	24 hrs	95°C	0.49
HF - 10%	20 min	20°C	5.18
NH ₄ F:HF - 10%	20 min	20°C	0.84
1HF:10HNO ₃	3 min	20°C	1.48
1HF:100HNO ₃	3 min	20°C	0.16
DI H ₂ O	24 hrs	95°C	0.00
Na ₂ CO ₃ - 0.02N	6 hrs	95°C	0.16
NaOH - 5%	6 hrs	95°C	1.83


Total alkali content is approximately: 0.1wt% (Typical <0.05wt%)


Weathering: 1

Weathering is defined as corrosion by atmosphericborne gases and vapor such as water and carbon dioxide. Glasses rated 1 will almost never show weathering effects; those rated 2 will occasionally be troublesome, particulary if weathering products cannot be removed; those rated 3 require more careful consideration.

Optical Wavelength	Refractive Index	
435.8nm	1.5198	
467.8nm	1.5169	
480nm	1.5160	
508.6nm	1.5141	
546.1nm	1.5119	
589.3nm	1.5099	
643.8nm	1.5078	

Transmittance





Thermal Conductivity Thermal conductivity is a calculated value, and is equal to the product of the thermal diffusivity multiplied by specific heat multiplied by density of the glass.						
Temp (°C)	Diffusivity (cm ² /sec)	Specific Heat(J/gm-°K)	Conductivity (W/cm -°K)			
23	0.00601	0.768	0.0109			
100	0.00572	0.896	0.0122			
200	0.00546	0.998	0.0129			
300	0.00530	1.067	0.0134			
400	0.00522	1.110	0.0137			
500	0.00518	1.154	0.0142			