CORNING Laser Technologies



CLT 66G:

High-precision laser glass processing for up to Gen 6

The CLT 66G laser glass processing tool is designed for 24/7 manufacturing in an industrial environment, supporting a glass substrate size of up to GEN6 transfering into 1,500 mm x 1,850 mm.

The Corning Laser Technologies systems are developed in close cooperation with the speciality glass experts at Corning. Their material science and optics knowledge adds unique advantages to this laser glass cutting process.



Using ultra-short laser pulses, the CLT 66G cuts by material disassociation rather than ablation. The result is a very low surface roughness, increased as-cut edge strength and yield.

The Corning Laser Technologies process enables cutting fully strengthened glass, Corning[®] Gorilla[®] glass, unstrengthened glass, as well as other transparent glass and crystalline materials.



Key Benefits

- Free-form, net-shape or near net-shape cutting at up to 1m/s (depending on contur)
- Cuts: curved, straight, perpendicular and angled lines as well as holes and slots (depending on tool setup)
- Cuts glass from 0.4mm up to 6 mm in thickness
- Automatic/touch-free separation process (material dependend)
- Eliminates fluids and tooling required in traditional processing methods



Applications

Advanced multi purpose and flexible laser machining system for:

Processing Glass Substrates

- Automotive windshields, roofs, sidelites, backlites
- Automotive interior glass
- Consumer electronics
- Architectural glass
- Display technologies
- Coated substrates
- Thin glass
- Strengthened and non-strengthened glass
- Electronic components

This system is also extremely well suited for different kinds of Micro Materials Processing, such as:

Other Materials

 Cutting of OLED, PI, wafer, ceramic, plastic, and other brittle materials.

CLT 66G Technical Specifications

Mechanics	Machine base and vertical structure are made from solid granite blocks X-Y single or double gantry design available Z-axis motorized (CNC-axis) Machine optimized for high precision processing at high speed Class 1 laser safety chamber	
Axes	X-axis travel 1,700 mm Y-axis travel 2,000 mm Z-axis travel 80 mm max. traverse speed x/y-axis max. acceleration	Drive: linear motor ¹⁾ Drive: linear motor ¹⁾ Drive: rotation motor ¹⁾ up to 1,000 mm/s (pattern dependent) up to 10 m/s ² (pattern dependent)
Accuracy	Pattern accuracy	< +/- 100 µm for parts cut out of a GEN6 substrate ²⁾ Accuracy depends on pattern geometry and process speed
CNC-Control	TwinCat 3 CNC control for all machine functions (G-code)	
Operator Interface	Based on Microsoft Windows 10 with CLT HMI	
Machine Vision	Integrated in standard configuration for fiducial recognition	
Loading / Unloading	Manual loading of substrates / unloading of parts	
Options	Automation available for loading and unloading (e.g. tilt table, parts picking unit) Glass waste management MES connection	
Electrical Supply	Rating Power consumption (peak/ average)	400 Volts, 3Ph+N+PE, 50/60 Hz (transformer available) 23 kVA/ 15 kVA ³⁾ ; 13 kW/ 9 kW ¹⁾
Cooling	Rating (peak/ average) Consumption	7.0 kW/ 4.0 kW ³⁾ min. 15 l/min, max. 25 l/min ³⁾
Compressed Air	Supply pressure Consumption	min. 6 bar / max. 8 bar ³⁾ typ. 560 Nl/min
Exhaust Air from Machine Enclosure	Volume	min. 450 m³/h exhaust air³)
Exhaust Air from Process Head	Volume	up to 200 m ³ /h exhaust air ³⁾
Machine Vacuum	No requirement at customer site Will be provided by a side channel blower inside the equipment	
Machine Size and Weight	Dimensions, including electrical/ supporting cabinets, load/ unload units and waste glass management Size: Width x Depth x Height ³⁾ Weight	12,300 x 5,605 x 2,900 mm approx. 11,000 kg (depending on configuration)
Temperature	20 °C, Deviation +/- 2 °C , non condensing	

 $^{1)}$ Nominal travel range. Effective travel range may be reduced by use of multiple process

heads and/or cameras.

²⁾ Environmental controlled room required.

 $^{\rm 3)}$ These values may vary, depending on the tool configuration, e.g. type of laser source.

Specifications are subject to change without notice.

CORNING Laser Technologies

For more information: Tel: +49 89 / 899 48 28-0 E-Mail: CLT-info@corning.com www.corning.com/lasertechnologies



© 2022 Corning Incorporated. All Rights Reserved. Corning is a registered trademark of Corning Incorporated, Corning, NY. Corning Incorporated. One Riverfront Plaza, Corning, NY 14831-0001

Corning / Specialty Materials /Corning® Laser Technologies/ Product Information Sheet January 2022