




# BRING BROADBAND HOME

Optical Tap
Architecture
Guide



Whether your deployment is centralized split, distributed split, or optical tap, you can count on our fiber-to-the-home expertise. Optical tap architectures are the most fiber lean. Asymmetric/uneven split terminals allow for single-fiber distribution of concatenated terminals. Routes are custom configured to optimize link loss. We've compiled the most commonly used preconnectorized products for optical tap. This document outlines two methods of deploying the distribution portion of the network depending on the level of connectivity used.

Our broad portfolio of products addresses your specific challenges from speed of deployment, labor and cost considerations, performance requirements, future-readiness, and more.

Select your options across these areas of the network:

- (A) Central Office (CO)
- (B) Feeder Cable
- (C) Fiber Distribution Hub (FDH)
- (D & E) Distribution Segment
- (F) Customer Premises

### Cost Components Comparison

### Labor Effort

Level of connectorization impacts crew & size



Full Splice Spliced Terminals Full Preconnectorized

### Material Cost

Level of connectorization impacts upfront cost



Full Splice

Spliced Terminals

\$ \$

Full Preconnectorized

\$ \$ \$ \$

### **Total Cost**

Labor effort and material cost drive total cost



Full Splice

Spliced Terminals

Full Preconnectorized

(8) (8) (8)

### **Connectivity for the Win!**

We are willing to bet on connectivity for your build. Decades of experience with connectivity have proven a wise investment for network operators around the world.

Your next deployment's fully connectorized design is on us.

Reach out to our subject matter experts to get your consultation started at connect@corning.com.

### **Optical Tap Option 1**

### **Spliced Closures**

The optical tap option shown on this page highlights a spliced design. Note: Optical tap networks may employ leading splitters that traditionally would be spliced in at a closure.

### Cost Components Comparison

### Labor Effort

Eliminates splice events downstream of splitter cabinet

222


#### **Material Cost**

Pre-installed connectors along distribution cable increase material cost

\$ \$

#### **Total Cost**

Savings result from reduction of splice events and cable placement labor



### A Central Office (CO)



The Centrix™ hardware system is a pay-as-you-grow solution where you can choose to order fully loaded racks/frames on day one, or simply start with a cassette in a housing. The core of the solution is a single, modular cassette that can be tailored to include a variety of optical devices and can contain up to 36 LC connector adapters.

#### **B** Feeder Cable



Whether aerial or buried, we have the fiber count, quality, and reliability your network demands. For higher fiber counts, ribbon cable may be a good option for you! For below-grade applications, consider using an armored cable. If you are looking for a solution to place in congested ducts with microducts, MiniXtend® cable may be the right fit.

### **C** Closure



Whether your FTTH network design has closures in a buried or aerial environment, one thing remains the same: you need assured environmental protection and quick, incremental subscriber drops. Our preconnectorized terminals are thoughtfully designed to incorporate individual strain-relief, sealing of all cables, and quick-release clamps for easy re-entry.

### **D** Distribution



Depending on your deployment method and architecture type, cable attributes may vary from self-support to armored or even microduct suitable cables. In the distribution, cables chosen may or may not be identical to the feeder depending on the serving area's needs.

### **E** Optical Tap Closures



By combining two splitters in each closure, one asymmetric 1x2 and one even 2-4- or 8-way splitter, the entire optical tap chain becomes plug and play.

### **F** Customer Premises



Corning's drop cable portfolio and associated assemblies allow for full plug-and-play at the subscriber premises and also support field-installable terminations.

### **Optical Tap Option 2**

#### Full Preconnectorized

The optical tap option shown on this page highlights a full preconnectorized design. Note: Optical tap networks may employ leading splitters that traditionally would be spliced in at a closure.

### Cost Components Comparison

#### Labor Effort

Eliminates splice events downstream of splitter cabinet

8

#### Material Cost


Pre-installed connectors along distribution cable increase material cost

\$ \$ \$ \$

#### **Total Cost**

Savings result from reduction of splice events and cable placement labor





### A Central Office (CO)



The Centrix™ hardware system is a pay-as-you-grow solution where you can choose to order fully loaded racks/frames on day one, or simply start with a cassette in a housing. The core of the solution is a single, modular cassette that can be tailored to include a variety of optical devices and can contain up to 36 LC connector adapters.

#### **B** Feeder Cable



Whether aerial or buried, we have the fiber count, quality, and reliability your network demands. For higher fiber counts, ribbon cable may be a good option for you! For below-grade applications, consider using an armored cable. If you are looking for a solution to place in congested ducts with microducts, MiniXtend® cable may be the right fit.

### Closure



Whether your FTTH network design has closures in a buried or aerial environment, one thing remains the same: you need assured environmental protection and quick, incremental subscriber drops. Our preconnectorized terminals are thoughtfully designed to incorporate individual strain-relief, sealing of all cables, and quick-release clamps for easy re-entry.

### **D** FlexNAP System



The FlexNAP system utilizes optical fiber cables upon which network access points are pre-installed at customerspecified locations along the length of the cable. In this design, the FlexNAP system has single-fiber Pushlok™ tethers that begin an optical tap chain of terminals.

### E Optical Tap Terminals



By combining two splitters in each terminal, one asymmetric 1x2 and one even 2-4- or 8-way splitter, the entire optical tap chain becomes plug and play.

### F Customer Premises



Corning's drop cable portfolio and associated assemblies allow for full plug-and-play at the subscriber premises and also support field-installable terminations.

### **Product Ordering Information**



B Feeder Cable				
Part Number	Description			
Ribbon Cables 🗸				
xxxZC5-14100D53	SST-Ribbon™ Armored Cable (144-864 fibers)			
xxxEC4-14100D53	SST-Ribbon All-Dielectric, Non-Armored (012-216 fibers)			
xxxEV4-14100D53	SST-UltraRibbon™ All-Dielectric, Non-Armored (288-864 fibers)			
xxxEV4-44101D53	RPX® All-Dielectric Self-Supporting Cable (024-144 fibers)			
Loose Tube Cables				
xxxZU4-T4F22D20	ALTOS® Loose Tube Cable (012-288 fibers)			
xxxZUC-T4F22D20	ALTOS Lite Single-Jacket, Armored (012-288 fibers)			
Microduct Cables 🗸				
xxxZM4-T4F22A20	MiniXtend® Cable (012-144 fibers)			
xxxZH4-Y4F40A20	MiniXtend HD Cable (144-288 fibers)			
xxxZH4-S4F40A20	MiniXtend HD Cable (288-432 fibers)			


	Fiber Distribution Hub (FDH)		
Part Number		Description	
Closures			
FDC-08M	1-G-NON-01Q-A-00-U	Fiber Dome Closure, 8 S12 ports, 1 2543-D-XSB tray, 4 single fusion splice holder (48 SF), 2 RF splice holder (144 RF), 1 ground, 2 trays max	
FDC-08S	-G-NON-01R-A-00-U	Fiber Dome Closure, 8 S12 ports, 1 2543-D tray, 8 single fusion splice holder (96 SF), 4 RF splice holder (288 RF), 1 ground, 2 trays max	
SCA-9T24-LRS-U		SCA Aerial Terminal, SNAP-9T24, standard end caps, direct fusion splicing, 16 drop ports	

D Option 1: Distribution Cable			
Part Number	Description		
Ribbon Cables			
xxxZC5-14100D53	SST-Ribbon Armored (144-864 fibers)		
xxxEC4-14100D53	SST-Ribbon Dielectric, Non-Armored (012-216 fibers)		
Loose Tube Cables			
xxxZU4-T4F22D20	ALTOS Loose Tube Cable (012-288 fibers)		
xxxZUC-T4F22D20	ALTOS Lite Armored Loose Tube Cable (012-288 fibers)		
Microduct Cables			
xxxZM4-T4F22A20	MiniXtend Cable (012-144 fibers)		
xxxZH4-Y4F40A20	MiniXtend HD Cable (144-288 fibers)		

<b>D</b> Option	າ 2: FlexNAP™ System		
Part Number	Description		
FlexNAP Trunk Cables			
FNAP-CBL-xxxEU4	FlexNAP Distribution Trunk Cable, ALTOS loose tube cable, dielectric, xxx fibers (012 -432 fibers)		
FNAP-CBL-xxxEUC	FlexNAP Distribution Trunk Cable, ALTOS loose tube cable, armored, xxx fibers (012-432 fibers)		
FlexNAP Tether Attachment Points			
FSD4AxxD1TN010F	FlexNAP Tether Attachment Point, ALTOS loose tube cable, dielectric, Pushlok connector, aerial, xx tether count (01 = single tether or 02 = dual tether)		
FSD4CxxD1RN015F	FlexNAP Tether Attachment Point, ALTOS loose tube cable, dielectric, low-profile (up to 72-fiber only), below grade, xx tether count (01 = single tether or 02 = dual tether)		
FSDCAxxD1RN015F	FlexNAP Tether Attachment Point, ALTOS loose tube cable, armored, Pushlok connector, aerial, xx tether count (01 = single tether or 02 = dual tether)		

Е	E Option 1: Optical Tap Closures	
Part Number		Description
Splice Closures* ✓ ■		
BPEO-S1	5-AMX-U	BPEO Splice Closure Size 1.5, MiniXtend
BPEO-DT	P-1-832-43xx-3ZZC1*	BPEO 2-port Optical Tap Tray with SC APC
BPEO-DT	P-1-832-45xx-3ZZC1*	BPEO 4-port Optical Tap Tray with SC APC
BPEO-DTP-1-832-49xx-3ZZC1*		BPEO 8-port Optical Tap Tray with SC APC
*xx indicat	es asymmetric split ratio	

E Option 2	: Optical Tap Terminals		
Part Number	Description		
2-port Terminals			
DTA4X21500NC00S0P-U	Evolv® Optical Tap Terminal, 2-port, 90/10 power split		
DTA4X21300NC00S0P-U	Evolv Optical Tap Terminal, 2-port, 85/15 power split		
DTA4X21100NC00S0P-U	Evolv Optical Tap Terminal, 2-port, 80/20 power split		
DTA4X20900NC00S0P-U	Evolv Optical Tap Terminal, 2-port, 70/30 power split		
DTA4X20800NC00S0P-U	Evolv Optical Tap Terminal, 2-port, 60/40 power split		
DTA4X20400NC00S0P-U	Evolv Optical Tap Terminal, 2-port, 00/00 power split		
4-port Terminals			
DTA8X41700NC00S0P-U	Evolv Optical Tap Terminal, 4-port, 90/10 power split		
DTA8X41600NC00S0P-U	Evolv Optical Tap Terminal, 4-port, 85/15 power split		
DTA8X41500NC00S0P-U	Evolv Optical Tap Terminal, 4-port, 80/20 power split		
DTA8X41200NC00S0P-U	Evolv Optical Tap Terminal, 4-port, 70/30 power split		
DTA8X41100NC00S0P-U	Evolv Optical Tap Terminal, 4-port, 60/40 power split		
DTA8X40700NC00S0P-U	Evolv Optical Tap Terminal, 4-port, 00/00 power split		
8-port Terminals			
DTB4X82000NC00S0P-U	Evolv Optical Tap Terminal, 8-port, 90/10 power split		
DTB4X81800NC00S0P-U	Evolv Optical Tap Terminal, 8-port, 85/15 power split		
DTB4X81700NC00S0P-U	Evolv Optical Tap Terminal, 8-port, 80/20 power split,		
DTB4X81500NC00S0P-U	Evolv Optical Tap Terminal, 8-port, 70/30 power split		
DTB4X81400NC00S0P-U	Evolv Optical Tap Terminal, 8-port, 60/40 power split		
DTB4X81000NC00S0P-U	Evolv Optical Tap Terminal, 8-port, 00/00 power split		
Terminal Jumpers			
D1D101EB49RxxxF-P-U	ROC™ Drop Cable, Pushlok® Jumper, dielectric, xxx feet		
DIDIOIED49NXXXI 1 -0			



## Build America, Buy America Act (BABAA) Compliance

- ✓ Produced in the United States: Meets requirements of the Build America, Buy America Act (BABAA), and 2 C.F.R. 184. All fiber, cable, and preform manufacturing occurs in the United States. For each manufactured product, at least 55% of the content is produced in the United States
- Waived: Meets requirements of NTIA's Limited General Applicability, Nonavailability Waiver of the Buy America Domestic Content Procurement Preference as Applied to the BEAD Program.
- Suggested de Minimis: Minor hardware that Corning believes will not exceed the thresholds under the de minimis waiver. De minimis products may cumulatively comprise up to the lesser of 5% of the total applicable project costs, or \$1,000,000.



To meet your requirements, we've nurtured long-term relationships with authorized distributors who stock our products and further support your needs including training, customer needs assessment, logistics, and equipment. Whether you are an end user, contractor, or installer, connect with our authorized distributors to purchase your Corning solution today.















### **CORNING**