



Network Solutions Designed for the Enterprise

Future-Flexible. Cost Effective. Extended Reach.

The Network Architecture Your Business Needs

As employees, residents, guests, patients, and students bring more devices into a space, they bring a new level of connectivity demands. Building owners need networks that can keep up with increasing technology requirements.

Whether you are planning for the next generation of Wi-Fi or adding IP devices like audio/visual, security cameras, building management, and IoT, Corning's solutions are built specifically for the needs of your enterprise.

This guide will highlight the best practices for a smart technology strategy – one that can go the distance, adapt as network requirements change, and scale as technology plans grow.



Inside this Guide

Key Challenges

Best Practices for a Smarter Technology Strategy...pg. 2

ActiFi Composite Cable

Build a future-flexible foundation...pg. 3

Remote Power Solutions

Deliver DC power to the edge of the network...pg. 5

Unmanaged Solutions

Leverage long-reach network capabilities...pg. 7

Fully-Managed SD-LAN

Gain ultimate flexibility and visibility to the edge...pg. 9

SD-LAN Family Spec Sheet

and network topology example...pg. 11



Best Practices for a Smarter Technology Strategy

1. Enable remote applications with long-reach connectivity solutions

Today's technology demands are testing the limits of legacy Category cable networks. Without long-reach solutions, building owners are faced with space constraints, limited local power, and unplanned connectivity needs that drive up network complexity and deployment costs. Corning's in-building network solutions extend the reach of the network to deliver unlimited data and Class 2 power out to the very edge of the network.

2. Stay ahead of future technology needs with a flexible, adaptable network

With new technologies coming onto our networks at an unprecedented rate, networks that can accommodate these ever-increasing technology demands can help businesses evolve as their technology needs change. Corning's flexible solutions help transform your technology program into a strategic asset.

3. Expand technology plans with scalable, future-ready connectivity

Smart technology strategies are built on future-ready infrastructure. Building owners who deploy unlimited bandwidth and power to the edge can seamlessly add new technologies to their networks. Unlike legacy Category cable networks, Corning's solutions can help building owners protect their technology investment by eliminating routine rip-and-replace infrastructure upgrades.

ActiFi Composite Cable

Achieve ultimate flexibility by bringing together the future-ready bandwidth capabilities of Single Mode optical fiber and the powering capabilities of copper with Corning's ActiFi Composite Cable. Composite cable has both fiber and copper conductors under the same cable jacket to deliver data and power to the very edge of your network.

Advantages

1. Save Pathway Space

Legacy Category cable networks rely on routine rip-and-replace upgrade cycles and single-purpose infrastructure which leads to crowded pathways and complexity. ActiFi Composite Cable streamlines your infrastructure onto a single cable allowing you to overcome space constraints.

2. Protect Your Technology Investment

With a future-ready cable, your business can protect your infrastructure investment by leaving your ActiFi composite cable in place during your next technology refresh. Put your technology funds to smarter use by avoiding costly routine rip-and-replace Category cable upgrades.


3. Speed Up Your Deployment

Keep your project schedule on track by saving time with your network deployment. ActiFi eliminates the need to pull separate cables for data and power which saves you valuable time. [Watch](#) how this installer deployed 11 ActiFi cables at once with Reel-in-a-Box.


4. Stay ahead of Future Technology Needs

Increasing Wi-Fi demands is one of the main drivers that is challenging building owners to design their networks with future-ready infrastructure, like ActiFi Composite Cable. Learn why the next generation of technologies will require optical fiber with this 3 minute read: [Enabling a Wireless World](#).


Legacy Category Cable Network




ActiFi Composite Cable



ActiFi Reel-in-a-Box Deployment



Overcome bandwidth and distance limitations with fiber






Applications

ActiFi is a Class-3 rated composite cable that supports low voltage (Class 2, 57 VDC/100 V) as well as bulk power solutions. Because ActiFi can reach distances over 2,000 feet, this cabling choice is also ideal for long-reach or remote applications such as security cameras in a parking area or outdoor campus-wide Wi-Fi.

ActiFi can support devices directly or via a connection to an edge device such as a media converter or software-defined access node (SDAN). ActiFi cable is compatible with Corning's Intelligent Power Solutions, 10G HPOE Media Converter, Software-Defined LAN (SD-LAN) portfolio, Small Cell, and Distributed Antenna Solutions (DAS).

ActiFi Cable Management

ActiFi is also compatible with Corning's structured cabling, hardware, and housing portfolios including CCH and EDGE. An example below shows how CCH cassettes and housings easily manage ActiFi composite cable. Flexible keystone adapters accept both fiber and power connector types.




Key Specs

Find the right cable for your project with Corning's broad portfolio of ActiFi composite cable. A few key specs are highlighted below. For a complete list of offerings, please visit our [ActiFi Cable Ordering Guide](#).

Highlights

Configurations	1-24 fibers and 2-12 copper conductors
Copper Conductors	20-12AWG
Environments	Indoor, Indoor/Outdoor (FREEDM)
Jacket Ratings	Riser, Plenum
Deployment Options	Bulk cable or Reel-in-a-box (500 feet/box or 1,000 feet/box)



Contact your local Corning Sales Engineer for a complementary sample box of ActiFi Cables.



Intelligent, Remote Power Solutions

Overcome PoE distance limitations of legacy Category networks by Injecting DC power into your network. Corning's expanded portfolio of high-density, Class 2 remote power solutions support intelligent power aggregation at the edge to deliver up to 800W of power. Our power solutions are compatible with Corning's ActiFi Composite Cable, connectivity, hardware, and actives portfolio.

Corning recommends that all designs using the Corning Remote Power Solution comply with the latest editions of the NEC of the NFPA, OSHA, and all applicable Local and State codes.

Advantages

1. Solve for Increasing Power Requirements

As buildings get smarter, they demand more power from our networks. Deliver up to 800W of power to the edge to support small to medium power loads such as IP devices and smart lighting.

2. Reduce Deployment Cost

Eliminate costly local power outlets and telecommunication rooms by delivering DC power across distance of 2,000 feet or more.

3. Save Space

Our new intelligent power solutions deliver up to 167% greater port density to help you solve for more power with a smaller footprint.


4. Gain Flexibility

Our new power supplies are a half rack unit wide and can be stacked side-by-side, wall-mounted, or installed inside an enclosure. With an ambient temperature range of -30C to +65C, these solutions can be deployed in various locations.

5. Simplify Power Management

With intelligence built in, this new power solution can be managed to allow current / voltage monitoring, faults monitoring, ports on/off control, prioritization & optimization.


Consolidated power distribution
at a single location



[Learn more](#) from
our expert Steve Letke



[Remote Power Overview](#)



[Use Cases](#): Security & Wi-Fi





Go the Distance

Extend the reach of your network beyond the 100-meter distance limitation of legacy Category networks. Enable remote applications at distances of 2,000 feet or more with Corning's Intelligent Power Solutions and ActiFi Composite Cable.

Use this distance table to build the right end-to-end network for your project based on the specific power requirements at the edge. Contact your local Corning Sales Engineer for assistance.

ActiFi™ Composite Cable Distances 1 pair Low voltage (57VDC)			
	30 Watts	60 Watts	75 Watts
20 AWG	590 ft.	295 ft.	235 ft.
18 AWG	940 ft.	470 ft.	375 ft.
16 AWG	1,500 ft.	750 ft.	600 ft.
14 AWG	>2,000 ft.	1,190 ft.	950 ft.
12 AWG	>2,000 ft.	1,895 ft.	1,500 ft.


Key Specs

Corning's expanded portfolio of Intelligent Power Solutions includes: new power supplies, power aggregators, step down converters, hardware, and accessories.

Highlights		
New Power Supplies	Achieve ultimate port density to deliver more power with less space.	16 port (1.5 RU tall, half RU wide) 32 port (2 RU tall, half RU wide)
Aggregators	Aggregate multiple 24V to 56V Class 2 inputs to provide more power (up to 800w of power to a single device) and redundancy at the edge.	2:1 or 8:1
Step Down Converter	Add this device to support both 56V and 24V loads from the same power supply	x1 output or x2 output
Accessories	Gain deployment flexibility with various mounting options.	Din rail mounting Rack shelves Cable management




Power Supply Unit
(PSU6 / PSM-I)



New 16-Port Intelligent
Power Supply (CIP)



2:1 Aggregator



Step Down Converter
x2 outputs



Unmanaged Networks with Extended Reach

Security cameras across a parking area, blanket Wi-Fi throughout a campus, and access controls around a perimeter are just a few examples of technologies that test the 100-meter distance limitation of Category cable networks. These network limitations lead to maxed-out pathways, space constraints, and costly local power outlets. Enabling these seemingly simple devices often takes a network deployment that can be quite complex. Corning’s portfolio of unmanaged, long-reach solutions can provide the cost-effective, “set it and forget it” connectivity you need at the edge. We provide two solutions: 10G HPoE Media Converters and an end-to-end Touchless Networking Solution.

10G 90W HPoE Media Converter

Corning’s new 1-port media converter solution is the industry’s first cost-effective media converter to support both 10G speeds and provide HPoE. It is compatible with Corning’s end-to-end fiber, power, hardware, and connectivity solutions and is also interoperable with existing copper or fiber switches. This cost-effective solution reduces network deployment costs by 45% compared to alternate media converter solutions.

Key Specs


- Supports 90W PoE++ (HPoE) and is backwards compatible to support PoE, PoE+, PoE++ (60W) / 802.3bt.
- Supports 10G speeds and is backwards compatible to support 1G or 2.5G speeds
- Allows for deployment flexibility with DIN-rail mounting and small form factor
- Interoperable with existing copper or fiber switches

Ordering Information


1LAN-FMC-10G	Media Converter
1LAN-FMC-DINBRACKET	DIN Rail Bracket
1LAN-SDAN-DIN1160	DIN Rail
1LAN-D600-ENC-3	NEMA4 Enclosure
1LAN-SFPP-10G-BXD-I	BiDi SFP+ 1330nm-TX/1270nm-RX
1LAN-SFPP-10G-BXU-I	BiDi SFP+ 1270nm-TX/1330nm-RX
1LAN-SFPP-10LR	10Gb/s SFP+ SMF

Fiber to the Edge Deployment Examples

Scenario 1: Leverage an Existing Copper Switch



Scenario 2: Leverage an Existing Fiber Switch





Touchless Networking Solution

Corning Touchless Networking is a self-provisioning network that leverages the benefits of a fiber- and power-deep architecture to enable simple, unmanaged applications in hard-to-reach places.

Touchless Networking is ideal for projects with phased budgets or future technology needs because it can seamlessly upgrade to a fully-managed software-defined LAN (SD-LAN) solution without rip-and-replacing the network. Simply activate the platform-as-a-service to turn this “set it and forget it” network into a fully-managed SD-LAN solution that can adapt to more complex networks like WLAN (multiple SSIDs) or audio/visual applications.

Case Study

A sports stadium needed to connect 48 remote, outdoor security cameras but had limited local power options. They leveraged Touchless Networking and saved 50% on their network deployment compared to a legacy Category network. With this future-ready capability in place, they can seamlessly upgrade to a fully-managed SD-LAN solution to add day-two applications such as outdoor Wi-Fi.


Resources

Learn more by visiting the [solution overview](#) to find use cases, kitted offerings, and ordering information. Or, check out this [5 minute video](#) with expert Ron Wells as he explains Touchless Networking in more detail.



*Touchless Networking Edge Kit
3-port SDAN in outdoor enclosure*

Fiber to the Edge Deployment Example






Fully-Managed, Future-Flexible Networks

For ultimate flexibility and visibility to the edge of your network, Corning's Fully-Managed Software-Defined LAN (SD-LAN) Solution is built on the future-ready foundation and long-reach capabilities of our ActiFi Composite Cable and Intelligent Power Solutions. As technology plans grow and evolve, network demands become more complex. We designed our SD-LAN solution specifically for the needs of the enterprise.

Our fully-managed SD-LAN solution can be integrated by our approved Everon Partners. To find a partner to help you with design and integration, please contact your local Corning Sales Engineer.

Fiber to the Edge Network Architecture



Advantages

1. Adapt as Network Requirements Change

Corning's SD-LAN solution is flexible by supporting two transport technologies within the same platform. Our dual-mode solution supports both point-to-multipoint (PON / GPON / XGSPON) and point-to-point (Active Ethernet), allowing for maximum adaptability as technology needs change.

2. Scale & Expand Your Tech Strategy

With a future-ready infrastructure in place, your enterprise can seamlessly scale to add more devices as your technology strategy evolves without having to pull additional cable.

3. Extend Your Network Reach to Save Space and Cost

Deliver connectivity beyond 2,000 feet or more. Reclaim revenue-generating space by reducing telecommunication rooms. Reclaim technology funds by reducing TR build-out and maintenance costs.

4. Simplify Network Management

Maximize your time with a single pane of glass orchestration platform that allows for template-based provisioning, remote troubleshooting, and visibility to the very edge of the network. Contact your local Corning Sales Engineer for a demo of our [Advanced Orchestration and Management Platform](#).



End-to-End Solution

Innovation is in our DNA. From the day we introduced the first viable low-loss optical fiber in 1970, we have been building on this innovation by expanding our in-building network expertise. In addition to our broad portfolio of cable, connectivity, hardware, and intelligent power, Corning also specializes in network actives and software, including:



- Whitebox appliances (1G/10G/40G Optical Switching Fabrics and PoE, PoE+, and PoE++) with a full SFP portfolio
- Intelligent software-defined access nodes for optical to Ethernet conversion and PoE
- Advanced Software Defined Network Orchestration Software

Applications & Case Studies


Enterprises from [hospitality](#), [education](#), [senior living](#), multi-family, manufacturing, [smart buildings](#), and beyond can make the most of their technology investment with a fully-managed SD-LAN solution. To learn more about how to transform your technology program, check out this 3-minute read: [4 Considerations for a Smarter Network](#).

Case Study	Size	Applications	Network Savings*
Medium Office	51,000 sq ft 70 employees	Wi-Fi, Security cameras, Sound masking, Voice, Cellular, Displays	34%
Large Office	180,000 sq ft 800 employees	Wi-Fi, Security cameras, Sound masking, A/V, Cellular, 4K displays	29%
Education Campus	14 buildings 2,000 drops	Wi-Fi, Voice, Data, A/V, Security cameras	48%
Senior Living	24 floors	Resident Wi-Fi, VoIP Phones, IPTV, Security	29%
Small Hotel	109 Rooms	WiFi in each room, IPTV, VoIP Phones	12%
Large Hotel	513 Rooms	WiFi in each room, IPTV, VoIP Phones	10%



*Compared to a legacy Category cable network deployment.









SDAN deployment examples from left to right: SDAN mounted in base of light pole, concealed behind wall face plate, installed on rack tray, deployed above ceiling to feed security camera, and hidden behind TV mount to deliver triple-play










SD-LAN Family Spec Sheet

Control Planes (Servers)	PART NUMBER	Description
	1LAN-SRV-50195L	1RU rack-mountable server for VNETC, VFC and Virtual Apps
	1LAN-SRV-50195L-2	1RU rack-mountable server for VNETC, VFC and Virtual Apps; > 600 SDANs

Data Planes (SDDP)	PART NUMBER	SFP+	QSFP+	GPON	POE	POE BUDGET	REDUNDANT POWER
	1LAN-SDDP-48P	48	6				Y
	1LAN-SDDP-24POE	4			(24) 30W (8) 60W	960W	Y
	1LAN-SDDP-48POE	4			(48) 30W (8) 60W	1650W	Y
	1LAN-SDOLT-0587	2		4			Y
	1LAN-SDOLT-0588	2		8			Y






Access Nodes (SDAN) and Media Converters (FMC)	Part Number	GE Ports	10GE Ports	PoE	PoE Budget	Notes
	1LAN-SDAN-8011	1	N/A	Yes, 60W	60W	SC APC Optical Connector
	1LAN-SDAN-8293	3	N/A	Yes, 30W	30W	SC APC Optical Connector
	1LAN-SDAN-IW4P	4	N/A	Yes, 60W	60W	SC APC Optical Connector
	1LAN-SDAN-7290*	4	N/A	Yes, 30W	60W	SC APC Optical Connector
	1LAN-SDAN-7298	8	N/A	Yes, 60W	140W	SC APC Optical Connector
	1LAN-SDAN-7691	5	1	Yes, 60W	140W	SFP+ Interface SC APC for PON LC UPC for Active Ethernet
	1LAN-FMC-10G Media Converter	0	1	Y, 90W	90W	**Media Converter SFP+ Interface LC UPC for 10G Transceiver

ActiFi Composite Cable delivers data and power beyond 2,000 ft.

Edge



















SDAN converts optical to Ethernet and delivers PoE to end devices



Transceivers	Part Number	Media	Rate	Max Range	Notes
	1LAN-SFP-1GCU	Cu	1Gb/s	100m	RJ-45
	1LAN-SFP-10G-T	Cu	10Gb/s	30m	RJ-45
	1LAN-SFP-1GB-LXLH	SMF	1Gb/s	10km	LC UPC Duplex
	1LAN-SFP-4305BC	SMF, bi-di	1Gb/s	10km	LC UPC Simplex
	1LAN-SFP-3405BC	SMF, bi-di	1Gb/s	10km	LC UPC Simplex
	1LAN-SFPP-10LR	SMF	10Gb/s	10km	LC UPC Duplex
	1LAN-SFPP-10SR	MMF	10Gb/s	300m	LC UPC Duplex
	1LAN-SFPP-10G-BXU-I	SMF, bi-di	10Gb/s	10km	LC UPC Simplex
	1LAN-SFPP-10G-BXD-I	SMF, bi-di	10Gb/s	10km	LC UPC Simplex
	1LAN-QSFP-40LR4	SMF	40Gb/s	10km	LC UPC Duplex
	1LAN-QSFP-40SR4	MMF	40Gb/s	150m	LC UPC Duplex
	1LAN-SFP-0035	SMF	1.244Gb/s 2.488Gb/s	20km	SC UPC - Used with 1LAN-SDOLT-0587/8
	1LAN-SFPP-10G-OLT	SMF	10Gb/s	20km	SC UPC - Used with 1LAN-SDDP-48P
	1LAN-SFPP-10G-LTF7225	SMF	10Gb/s	20km	SC APC - Used with 1LAN-SDAN-7691



Power	Part Number	Description
	PSU6-1U	Power Supply Unit - 12 circuits - 57VDC, 97W Class 2 Limited Power Source. Supports up to 6 PSM-I Modules.
	PSM-I	Power Supply Module is used with PSU6-1U. Supports 2x97W 57VDC LPS Ports
	CIP-16-24V CIP-16-56V	Intelligent Power Supply Unit (16 ports, 24/56V)
	CIP-AGG-2	Aggregator: 2 Class-2 inputs
	CIP-AGG-8	Aggregator: 8 Class-2 inputs
	CIP-VC-56T24	Step down converter: Class-2 56Vdc to 24Vdc

Accessories	Part Number	Description
	1LAN-SDAN-SMCRD	Surface-Mount Cradle (8293 series)
	1LAN-SDAN-FST0004	Fiber Slack Tray (729x series)
	1LAN-SDAN-PWRSUP2	Software-Defined Access Node Local Power Supply Output - 54VDC @ 81Watts (1,3,4 port SDANs)
	1LAN-SDAN-PWRSUP160	Software-Defined Access Node Local Power Supply Output - 54VDC @ 150Watts (5,8 port SDANs)
	1LAN-D600-ENC-3	Outdoor enclosure for SDAN family (81XX, 82XX)
	1LAN-D600-ENC-8	Outdoor enclosure for SDAN family (729X, 769X)
	1LAN-PLS-A32LCA	1x32 PLC Splitter, 19-in rack, LC APC
	1LAN-PLS-A32SCA	1x32 PLC Splitter, 19-in rack, SC APC
	1LAN-D600-CCP2-WH	Power Keystone Adapter (connector style)
	1LAN-D920CC-6	Keystone CCH Panel
	DE2-CCA-1PR18-2M	1 Pair Power Cross Connect
	DE2-CCA-2PR18-2M	2 Pair Y-Power Cross Connect



Network Solutions Designed for the Enterprise

Whether you are facing space constraints, enabling long-reach applications, or refreshing your technology plans, Corning's in-building network solutions are built to help you design the network you need.

Built on the foundation of fiber-to-the-edge network architecture, Corning's end-to-end solutions deliver future-flexible data and power to the very edge of your network. This guide will help you choose the networking solution that best fits your project and show you how to seamlessly upgrade your network as technology plans change without having to routinely rip-and-replace your network infrastructure.

Learn more by visiting the
Next-Gen LAN Knowledge Center